


COMPONENTS	COLOR
ST CONNECTOR	METALLIC
SC CONNECTOR	BLUE
OFNR RATED SINGLE-MODE CABLE	YELLOW

Standard Lengths	
-1	1 meter
-2	2 meters
-3	3 meters
-5	5 meters
-10	10 meters
-15	15 meters
-XXX	Custom Length in meters



SPECIFICATIONS

POLISH: ULTRA PHYSICAL CONTACT
FIBER TYPE: 8.3/125 MICRONS



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE300004-XX

DES.

CABLE ASSEMBLY, ST TO SC SIMPLEX,
SINGLE MODE (9/125)

REV. B

FSCM NO. 53919

CAD FILE

102908

SCALE N/A

SIZE A

127

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN METERS.
4. LENGTH TOLERANCE IS -0/+0.153 METERS