


| COMPONENTS                   | COLOR    |
|------------------------------|----------|
| ST CONNECTOR                 | METALLIC |
| SC CONNECTOR                 | BLUE     |
| OFNR RATED SINGLE-MODE CABLE | YELLOW   |
|                              |          |

| Standard Lengths |                         |
|------------------|-------------------------|
| -1               | 1 meter                 |
| -2               | 2 meters                |
| -3               | 3 meters                |
| -5               | 5 meters                |
| -10              | 10 meters               |
| -15              | 15 meters               |
| -XXX             | Custom Length in meters |



# SPECIFICATIONS

POLISH: ULTRA PHYSICAL CONTACT  
FIBER TYPE: 8.3/125 MICRONS



**PASTERNAK ENTERPRISES, INC.**  
P.O BOX 16759, IRVINE, CA 92623  
PHONE (949) 261-1920 FAX (949) 261-7451  
  
WEB ADDRESS: [www.pasternack.com](http://www.pasternack.com)  
E-MAIL ADDRESS: [sales@pasternack.com](mailto:sales@pasternack.com)  
**COAXIAL & FIBER OPTICS**

|                    |                       |                                                         |           |            |
|--------------------|-----------------------|---------------------------------------------------------|-----------|------------|
| DWG TITLE          |                       | DES.                                                    |           |            |
| <b>PE300010-XX</b> |                       | CABLE ASSEMBLY, ST TO SC<br>DUPLEX, SINGLE MODE (9/125) |           |            |
| REV. B             | <b>FSCM NO. 53919</b> | CAD FILE 102908                                         | SCALE N/A | SIZE A 127 |

**NOTES:**  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN METERS.  
4. LENGTH TOLERANCE IS -0/+0.153 METERS