



0 to 42 dB Toggle Step Attenuator, BNC Female To BNC Female With 0.5 dB Step Rated To 1 Watt Up To 1 GHz

TECHNICAL DATA SHEET

PE7036-1

**0 to 42 dB Toggle Step Attenuator, BNC Female To BNC Female With 0.5 dB Step Rated To 1 Watt Up To 1 GHz**

**Configuration**

Design	Step, Bidirectional Attenuator
Connector 1	BNC Female
Connector 2	BNC Female
Body Material and Plating	Aluminum

**Electrical Specifications**

Frequency Range, MHz	DC to 1,000
Impedance, Ohms	50
Attenuation Value, dB	0 to 42
Step Size, dB	0.5
Step Type	Toggle
Maximum Input Power, Watts	1
Maximum Insertion Loss, dB	1.2
Maximum VSWR	1.4:1

**Frequency 1**

Range, MHz	DC to 500
VSWR	1.2:1
Attenuation Accuracy, dB	± 0.7

**Frequency 2**

Range, MHz	500 to 1,000
VSWR	1.4:1
Attenuation Accuracy, dB	± 1

**Mechanical Specifications**

**Size**

Length, in [mm]	5.67 [144.02]
Width, in [mm]	1.062 [26.97]
Height, in [mm]	1.062 [26.97]

**Connector 1**

Type	BNC Female
------	------------

**Connector 2**

Type	BNC Female
------	------------

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [0 to 42 dB Toggle Step Attenuator, BNC Female To BNC Female With 0.5 dB Step Rated To 1 Watt Up To 1 GHz PE7036-1](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



0 to 42 dB Toggle Step Attenuator, BNC Female To BNC  
Female With 0.5 dB Step Rated To 1 Watt Up To 1 GHz

TECHNICAL DATA SHEET

PE7036-1

**Compliance Certifications** (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

**Plotted and Other Data**

Notes:

Values at 25 °C, sea level

0 to 42 dB Toggle Step Attenuator, BNC Female To BNC Female With 0.5 dB Step Rated To 1 Watt Up To 1 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [0 to 42 dB Toggle Step Attenuator, BNC Female To BNC Female With 0.5 dB Step Rated To 1 Watt Up To 1 GHz PE7036-1](http://www.pasternack.com/42db-step-bnc-female-bnc-female-1-watt-attenuator-pe7036-1)

URL: <http://www.pasternack.com/42db-step-bnc-female-bnc-female-1-watt-attenuator-pe7036-1-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

# PE7036-1 CAD Drawing

0 to 42 dB Toggle Step Attenuator, BNC Female To BNC Female  
With 0.5 dB Step Rated To 1 Watt Up To 1 GHz




FIGURE 1




FIGURE 2

P/N	ATTEN.									FIGURE
	A	B	C	D	E	F	G	H	I	
PE7036-1	1	2	3	6	10	20				1
PE7036-2	.5	1	2	3	6	10	20	20	20	2
PE7036-3	1	2	3	6	10	20	20	20	20	2

VALUES ABOVE WILL BE PRINTED ON THE BODY

- NOTES:  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE  
**PE7036**

FSCM NO. 53919

CAD FILE 030613

SCALE N/A

SIZE A

2231

**PASTERNAK**  
 Pasternack Enterprises, Inc.  
 P.O. Box 16759 | Irvine | CA | 92623  
 Phone: (949) 261-1920 | Fax: (949) 261-7451  
 Website: www.pasternack.com | E-Mail: sales@pasternack.com