



0 to 42 dB Toggle Step Attenuator, 75 Ohm BNC Female To 75 Ohm BNC Female With 1 dB Step Rated To 1 Watt Up To 1 GHz

TECHNICAL DATA SHEET

PE7038-1

**0 to 42 dB Toggle Step Attenuator, 75 Ohm BNC Female To 75 Ohm BNC Female With 1 dB Step Rated To 1 Watt Up To 1 GHz**

**Configuration**

Design	Step, Bidirectional Attenuator
Connector 1	BNC Female
Connector 2	BNC Female

**Electrical Specifications**

Frequency Range, MHz	DC to 1,000
Impedance, Ohms	75
Attenuation Value, dB	0 to 42
Step Size, dB	1
Step Type	Toggle
Maximum Input Power, Watts	1
Maximum VSWR	1.4:1

**Frequency 1**

Range, MHz	DC to 1,000
Attenuation Accuracy, dB	± 1

**Mechanical Specifications**

**Size**

Length, in [mm]	5.6 [142.24]
Width, in [mm]	1.062 [26.97]
Height, in [mm]	1.062 [26.97]

**Connector 1**

Type	BNC Female
------	------------

**Connector 2**

Type	BNC Female
------	------------

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [0 to 42 dB Toggle Step Attenuator, 75 Ohm BNC Female To 75 Ohm BNC Female With 1 dB Step Rated To 1 Watt Up To 1 GHz PE7038-1](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



0 to 42 dB Toggle Step Attenuator, 75 Ohm BNC Female To 75 Ohm BNC Female With 1 dB Step Rated To 1 Watt Up To 1 GHz

## TECHNICAL DATA SHEET

PE7038-1

**Compliance Certifications** (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

### Plotted and Other Data

Notes:

Values at 25 °C, sea level

0 to 42 dB Toggle Step Attenuator, 75 Ohm BNC Female To 75 Ohm BNC Female With 1 dB Step Rated To 1 Watt Up To 1 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [0 to 42 dB Toggle Step Attenuator, 75 Ohm BNC Female To 75 Ohm BNC Female With 1 dB Step Rated To 1 Watt Up To 1 GHz PE7038-1](http://www.pasternack.com/42db-step-bnc-female-bnc-female-1-watt-attenuator-pe7038-1)

URL: <http://www.pasternack.com/42db-step-bnc-female-bnc-female-1-watt-attenuator-pe7038-1-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

# PE7038-1 CAD Drawing

0 to 42 dB Toggle Step Attenuator, 75 Ohm BNC Female To 75 Ohm  
BNC Female With 1 dB Step Rated To 1 Watt Up To 1 GHz




FIGURE 1




FIGURE 2

P/N	ATTEN.									FIGURE
	A	B	C	D	E	F	G	H	I	
PE7038-1	1	2	3	6	10	20				1
PE7038-2	.5	1	2	3	6	10	20	20	20	2
PE7038-3	1	2	3	6	10	20	20	20	20	2

VALUES ABOVE WILL BE PRINTED ON THE BODY

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE

**PE7038**

DWG TITLE

**PASTERNAK®**  
Pasternack Enterprises, Inc.  
P.O. Box 16759 | Irvine | CA | 92623  
Phone: (949) 261-1920 | Fax: (949) 261-7451  
Website: www.pasternack.com | E-Mail: sales@pasternack.com

FSCM NO. 53919

CAD FILE 022613

SCALE N/A

SIZE A

2231