


MATERIALS

BODY	BRASS NICKEL PLATED
CONTACT (M)	GOLD PLATED
CONTACT (F)	SILVER PLATED
INSULATOR	PTFE



SPECIFICATIONS

FREQUENCY RANGE: DC TO 1,000 MHz
 IMPEDANCE: 50 OHMS
 VSWR: 1.50:1 MAXIMUM

FUSE ELEMENT: 1/4 AMP

FUSE LEVEL: +35 dBm



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
 E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE7300-3

DES.

N FUSE HOLDER, FREQUENCY RANGE: DC TO 1,000 MHz

SIZE A

FSCM NO. 53919

CAD FILE 080902

SCALE N/A

127

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.