



SPECIFICATIONS

FREQUENCY RANGE: 100 KHz TO 40 GHz
 VSWR: 1.80:1 MAX
 ISOLATION (RF TO BIAS PORT) TYPICAL: 30 dB
 DC VOLT MAX: 25
 DC CURRENT MAX: 250 mA
 BIAS CONNECTOR: SMA FEMALE



PASTERNACK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
 E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE1609

DES.

BIAS TEE, 2.9mm MALE/FEMALE TO SMA FEMALE

Rev.-

FSCM NO. 53919

CAD FILE

102710

SCALE N/A

SIZE A

127

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.