

N Female Bulkhead to MMCX Plug Right Angle Semi-Flexible Precision Cable 6 Inch Length Using PE-SR405FLJ Coax, RoHS



TECHNICAL DATA SHEET

PE39464-6

Pasternack's formable cable assemblies are hand formable semi-rigid replacements that are an alternative to costly preformed assemblies. The formable semi-rigid cable alternatives are dimensionally and electrically similar to their semi-rigid counterpart and have a tinned-copper-braid outer shield that provides excellent RF shielding. The hand formable cable assemblies from Pasternack do not require special tooling to shape or reshape the assemblies and can replace standard semi-rigid versions. The assemblies are available with or without a FEP jacket and are RoHS compliant,

Features

- Dimensionally and electrically the same as standard, solid outer conductor semi-rigid coax
- Cable may be formed by hand and does not require special tools to bend
- May be formed more than once without damaging the outer conductor
- High RF Shielding >100 dB
- 100% Hi-pot and continuity tested
- 100% VSWR tested to max frequency of assembly
- Standard and custom lengths ship the same day

Configuration

Connector 1 Connector 2 Cable Type N Female Bulkhead MMCX Plug Right Angle PE-SR405FLJ

Electrical Specifications

Frequency Range Impedance Velocity of Propagation Group Delay RF Shielding

50 Ohms 69.5 % 1.43 ns/ft [4.69 ns/m] 100 dB

DC to 6 GHz

Performance by Frequency

Frequency 1

Frequency 250 MHz Insertion Loss 0.234 dB

Frequency 2

Frequency 500 MHz Insertion Loss 0.269 dB

Frequency 3

Frequency 1000 MHz Insertion Loss 0.298 dB

Frequency 4

Frequency 2.5 GHz Insertion Loss 0.347 dB

Frequency 5

Frequency 6 GHz

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to MMCX Plug Right Angle Semi-Flexible Precision Cable 6 Inch Length Using PE-SR405FLJ Coax, RoHS PE39464-6

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



N Female Bulkhead to MMCX Plug Right Angle Semi-Flexible Precision Cable 6 Inch Length Using PE-SR405FLJ Coax, RoHS



TECHNICAL DATA SHEET

PE39464-6

Insertion Loss 0.452 dB

Mechanical Specifications

Size

Length 6 in [152.4 mm]
Diameter 0.866 in [22 mm]

Cable Color Black

One Time Minimum Bend Radius 0.236 in [5.99 mm]
Repeated Minimum Bend Radius 0.787 in [19.99 mm]

Cable

Cable Type PE-SR405FLJ

Inner Conductor Type Solid

Cable Inner Conductor Copper Clad Steel, Silver

No of Shields 1
Dielectric Type PTFE
Jacket Material FEP

Jacket Diameter 0.098 in [2.49 mm]

Connector 1

Type N Female Bulkhead

Configuration Straight
Mount Method Bulkhead

Inner Conductor Material and Plating Phosphor Bronze, Gold

Body Material and Plating Brass, Nickel Dielectric Type PTFE

Connector 2

Type MMCX Plug Right Angle

Configuration Right Angle

Inner Conductor Material and Plating Phosphor Bronze, Gold

Body Material and Plating Brass, Gold Dielectric Type PTFE

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant Yes

REACH Compliant 06/18/2012

Plotted and Other Data

Notes:

• Values at +25 °C, sea level

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to MMCX Plug Right Angle Semi-Flexible Precision Cable 6 Inch Length Using PE-SR405FLJ Coax, RoHS PE39464-6

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





N Female Bulkhead to MMCX Plug Right Angle Semi-Flexible Precision Cable 6 Inch Length Using PE-SR405FLJ Coax, RoHS

TECHNICAL DATA SHEET

PE39464-6

How to Order



Example: PE39464-6-12 = 12 inches long cable

PE39464-6-100cm = 100 cm long cable

N Female Bulkhead to MMCX Plug Right Angle Semi-Flexible Precision Cable 6 Inch Length Using PE-SR405FLJ Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to MMCX Plug Right Angle Semi-Flexible Precision Cable 6 Inch Length Using PE-SR405FLJ Coax, RoHS PE39464-6

URL: http://www.pasternack.com/n-female-mmcx-plug-pe-sr405flj-cable-assembly-pe39464-6-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE39464-6 CAD Drawing

N Female Bulkhead to MMCX Plug Right Angle Semi-Flexible Precision Cable 6 Inch Length Using PE-SR405FLJ Coax, RoHS



Note: This part is lead free.

