

SMB Jack Bulkhead Mount Connector Crimp/ Solder Attachment for RG188-DS, RG316-DS

TECHNICAL DATA SHEET

PE45159

Configuration

Connector Connector Specification Connector Interface Type Attachment Method (Shield/Contact) Body Style Mount Method

Electrical Specifications

Frequency Range Impedance Maximum Operating Voltage Dielectric Withstanding Voltage

Mechanical Specifications

Temperature Operating Range

Size Length Width/Dia.

Weight

Connector

Type Contact Material and Plating Contact Plating Specification Body Material and Plating Body Plating Specification Dielectric Type

REACH Compliant

SMB Jack MIL-STD-348A RG188-DS, RG316-DS Crimp/Solder Straight Bulkhead

DC to 4 GHz 50 Ohms 335 Volts 1,000 Vrms

-65 to +165 deg C

1 in [25.4 mm] 0.25 in [6.35 mm] 0.005 lbs [2.27 g]

SMB Jack Brass, Gold 30µ in. minimum Brass, Nickel 100µ in. minimum Teflon

Compliance Certifications (visit www.Pasternack.com for current document) RoHS Compliant

06/18/2012

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMB Jack Bulkhead Mount Connector Crimp/Solder Attachment for RG188-DS, RG316-DS PE45159

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





SMB Jack Bulkhead Mount Connector Crimp/ Solder Attachment for RG188-DS, RG316-DS

TECHNICAL DATA SHEET

PE45159

Plotted and Other Data

Notes:

• Values at +25 °C, sea level

SMB Jack Bulkhead Mount Connector Crimp/Solder Attachment for RG188-DS, RG316-DS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMB Jack Bulkhead Mount Connector Crimp/Solder Attachment for RG188-DS, RG316-DS PE45159

URL: http://www.pasternack.com/smb-jack-rg188-ds-rg316-ds-connector-pe45159-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE45159 CAD Drawing

SMB Jack Bulkhead Mount Connector Crimp/Solder

Attachment for RG188-DS, RG316-DS

