



1 dB Fixed Attenuator, SMA Male To SMA Female Aluminum Heatsink Black Anodized Body Rated To 5 Watts Up To 3 GHz

TECHNICAL DATA SHEET

PE7391-1

1 dB Fixed Attenuator, SMA Male To SMA Female Aluminum Heatsink Black Anodized Body Rated To 5 Watts Up To 3 GHz

Configuration

Design	Fixed, Bidirectional Attenuator
Connector 1	SMA Male
Connector 2	SMA Female
Body Material and Plating	Aluminum Heatsink, Black Anodized

Electrical Specifications

Frequency Range, GHz	DC to 3
Impedance, Ohms	50
Attenuation Value, dB	1
Maximum Input Power, Watts	5
Maximum VSWR	1.2:1

Frequency 1

Range, GHz	DC to 3
VSWR	1.2:1
Attenuation Accuracy, dB	± 0.4

Mechanical Specifications

Temperature

Operating Range, deg C	-55 to +125
------------------------	-------------

Size

Length, in [mm]	2.756 [70]
Width, in [mm]	0.7 [17.78]
Weight, lbs [g]	0.143 [64.86]

Connector 1

Type	SMA Male
Contact Material and Plating	Brass, Gold
Coupling Nut Material and Plating	Brass, Nickel
Hex Size, Inch	5/16
Torque, in-lbs [Nm]	5 [0.57]
Body Material and Plating	Brass, Nickel

Connector 2

Type	SMA Female
Contact Material and Plating	Beryllium Copper, Gold
Body Material and Plating	Brass, Nickel

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [1 dB Fixed Attenuator, SMA Male To SMA Female Aluminum Heatsink Black Anodized Body Rated To 5 Watts Up To 3 GHz PE7391-1](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



1 dB Fixed Attenuator, SMA Male To SMA Female Aluminum Heatsink Black Anodized Body Rated To 5 Watts Up To 3 GHz

TECHNICAL DATA SHEET

PE7391-1

Compliance Certifications (visit www.Pasternack.com for current document)
RoHS Compliant Yes

Plotted and Other Data
Notes:

Values at 25 °C, sea level

1 dB Fixed Attenuator, SMA Male To SMA Female Aluminum Heatsink Black Anodized Body Rated To 5 Watts Up To 3 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [1 dB Fixed Attenuator, SMA Male To SMA Female Aluminum Heatsink Black Anodized Body Rated To 5 Watts Up To 3 GHz PE7391-1](#)

URL: <http://www.pasternack.com/1db-fixed-sma-male-sma-female-5-watts-attenuator-pe7391-1-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE7391-1 CAD Drawing

1 dB Fixed Attenuator, SMA Male To SMA Female Aluminum Heatsink
Black Anodized Body Rated To 5 Watts Up To 3 GHz



SMA FEMALE

FIGURE 1

SMA MALE

P/N	ATTEN.	FIGURE
PE7391-1	1 dB	1
PE7391-2	2 dB	1
PE7391-3	3 dB	1
PE7391-6	6 dB	1
PE7391-10	10 dB	1
PE7391-15	15 dB	1
PE7391-20	20 dB	1
PE7391-30	30 dB	1

DWG TITLE

PE7391

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

PE PASTERNAK®
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

FSCM NO. 53919

CAD FILE 042913

SCALE N/A

SIZE A

2231