



SPECIFICATIONS

FREQUENCY RANGE: DC TO 2 GHz
 PHASE ADJUSTMENT: 60° PER GHz
 OPTIMIZED FOR FULL RANGE
 INSERTION LOSS: .5 db MAX
 VSWR: 1.5:1 MAX
 RF POWER: 100 WATTS AVERAGE
 3000 WATTS PEAK



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
 E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE
PE8243

DES. SMA FEMALE PHASE SHIFTER
 FREQUENCY RANGE: DC TO 2 GHz

REV. -	FSCM NO. 53919	CAD FILE 042209	SCALE N/A	SIZE A	147
--------	-----------------------	-----------------	-----------	--------	-----

NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES.