



78 Ohm Flexible RG108 Twinax Cable Single Shielded with Black PVC Jacket

RF Cables Technical Data Sheet



Times Microwave Systems Coax Cable Specification Configuration

- Flexible Cable
- 1 Shield(s)

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
Impedance		78		Ohms
Velocity of Propagation		66		%
Nominal Capacitance		19.7 [64.63]		pF/ft [pF/m]

Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	10	100	200	400	700	MHz
Attenuation, Typ	2.8	9	13.6	19.4	26.4	dB/100ft
	9.19	29.53	44.62	63.65	86.61	dB/100m

Description	F6	F7	F8	F9	F10	Units
Frequency	900	1,000				MHz
Attenuation, Typ	30.4	34.6				dB/100ft
	99.74	113.52				dB/100m

Mechanical Specifications

0.235 in [5.97 mm] Diameter Weight 0.038 lbs/ft [0.06 Kg/m]

Construction Specifications

Description	Material and Plating	Diameter	
Inner Conductor	Copper, Tin7	0.038 in 0.97 mm	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 78 Ohm Flexible RG108 Twinax Cable Single Shielded with Black PVC Jacket RG108A/U

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451





78 Ohm Flexible RG108 Twinax Cable Single Shielded with Black PVC Jacket

RF Cables Technical Data Sheet



Conductor Type	Stranded	
Dielectric	PE	0.079 in 2.01 mm
First Shield	Tinned Copper Braid	0.185 in 4.7 mm
Jacket	PVC, Black	0.235 in [5.97 mm]

Environmental Specifications

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

78 Ohm Flexible RG108 Twinax Cable Single Shielded with Black PVC Jacket from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 78 Ohm Flexible RG108 Twinax Cable Single Shielded with Black PVC Jacket RG108A/U

URL: https://www.pasternack.com/78-ohm-flexible-rg108au-pvc-jacket-tinned-copper-braid-outer-conductor-single-shieldedblack-rg108a-u-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

