



Low PIM 3 Way N Equal-Tapper High Power From 600 MHz to 2.7 GHz Rated at 300 Watts

RF Tap Power Dividers Technical Data Sheet

PE-T1012

Features

- Optimized at Mobile Network Frequencies between 380 MHz to 6 GHz
- Low Loss and Low PIM, with VSWR as low as 1.15
- IP65 or IP67 Rated
- Available with High Power N or 7/16 DIN style connectors

Description

Pasternack's RF Tapper Power Dividers are designed to be wideband and low loss, with minimal reflections across Mobile Network bands between 380 MHz and 6 GHz. Their Air Dielectric and no Solder Joint designs make them ideal for indoor use, while the rugged construction ensures IP65 or IP67 outdoor performance.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.6		2.7	GHz
Impedance		50		Ohms
Input VSWR			1.3:1	
Insertion Loss			4.85	dB
Passive Intermodulation		-160		dBc
Input Power (CW)			300	Watts
Input Power (Peak)			3	KWatts

Mechanical Specifications

Size

 Length
 10.23 in [259.84 mm]

 Width
 3.2 in [81.28 mm]

 Height
 1 in [25.4 mm]

Weight 1.0243 lbs [464.61 g]

Housing Material and Plating Aluminum, Conversion Coating

Configuration

Package Type Connectorized Input Connector N Female Output Connector N Female

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Low PIM 3 Way N Equal-Tapper High Power From 600 MHz to 2.7 GHz Rated at 300 Watts PE-T1012

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



Low PIM 3 Way N Equal-Tapper High Power From 600 MHz to 2.7 GHz Rated at 300 Watts



RF Tap Power Dividers Technical Data Sheet

PE-T1012

Environmental Specifications

Ingress Protection (IP) Rating

IP67

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Low PIM 3 Way N Equal-Tapper High Power From 600 MHz to 2.7 GHz Rated at 300 Watts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Low PIM 3 Way N Equal-Tapper High Power From 600 MHz to 2.7 GHz Rated at 300 Watts PE-T1012

URL: https://www.pasternack.com/low-pim-3-way-n-equal-tapper-2.7-ghz-pe-t1012-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE-T1012 CAD Drawing

Low PIM 3 Way N Equal-Tapper High Power From 600 MHz to 2.7 GHz Rated at 300 Watts

