



COMPONENTS	IMPEDANCE
BNC MALE	50 OHM
BNC MALE	50 OHM
RG178B/U	50 OHM

Standard Lengths	
-12	12"
-24	24"
-36	36"
-48	48"
-60	60"
-XXX	Custom Length in inches





PASTERNAK ENTERPRISES®
ESTABLISHED 1972

PASTERNAK ENTERPRISES, INC.
P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE		DES. CABLE ASSEMBLY, RG178B/U, BNC MALE TO BNC MALE			
PE33130-XX		REV. -		FSCM NO. 53919	CAD FILE 082411
NOTES:		SCALE N/A			
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.		SIZE A 2231			
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.		NOTES:			
3. DIMENSIONS ARE IN INCHES [mm].		1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.			
4. LENGTH TOLERANCE IS ± 1.5% OR 10mm, WHICHEVER IS GREATER.		2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.			