
COMPONENTS	IMPEDANCE
BNC MALE	50 OHM
SMA MALE	50 OHM
RG178B/U	50 OHM

Standard Lengths	
-12	12"
-24	24"
-36	36"
-48	48"
-60	60"
-XXX	Custom Length in inches





RoHS Compliance Certified



PASTERNACK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

SCALE N/A

SIZE A 147

DWG TITLE **PE33258LF-XX** CABLE ASSEMBLY, RG178B/U, BNC MALE TO SMA MALE (LEAD FREE)

FSCM NO. 53919

REV. A

- NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.

CAD FILE 012208

- 3. DIMENSIONS ARE IN INCHES.
- 4. LENGTH TOLERANCE IS ± 1.5% OR ± 3/8", WHICHEVER IS GREATER.