

SMA Male to SMA Male Cable Using RG223 Coax with HeatShrink, LF Solder




PE3377LF/HS

Configuration

- Connector 1: SMA Male
- Connector 2: SMA Male
- Cable Type: RG223
- Coax Flex Type: Flexible

Features

- Max Frequency 12.4 GHz
- 66% Phase Velocity
- Double Shielded
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3377LF/HS SMA male to SMA male cable using RG223 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SMA cable assembly has a male to male gender configuration with 50 ohm flexible RG223 coax. The PE3377LF/HS SMA male to SMA male cable assembly operates to 12.4 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Operating Voltage (AC)			500	Vrms

Specifications by Frequency

SMA Male to SMA Male Cable Using RG223 Coax with HeatShrink, LF Solder



PE3377LF/HS

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	500	1000	2500	5000	11000	MHz	
PE3377LF/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.09	0.134	0.219	0.335	0.541	dB/ft	
			0.3	0.44	0.72	1.1	1.78	dB/m	
PE3377LF/HS-12	12 inch	Insertion Loss (Typ.)	0.29	0.34	0.42	0.54	0.75	dB	0.061
PE3377LF/HS-24	24 inch	Insertion Loss (Typ.)	0.38	0.47	0.64	0.87	1.29	dB	0.093
PE3377LF/HS-36	36 inch	Insertion Loss (Typ.)	0.47	0.61	0.86	1.21	1.83	dB	0.124
PE3377LF/HS-60	60 inch	Insertion Loss (Typ.)	0.65	0.87	1.3	1.88	2.91	dB	0.186
PE3377LF/HS-72	72 inch	Insertion Loss (Typ.)	0.74	1.01	1.52	2.21	3.45	dB	0.217

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.061 pounds
Additional Weight per Inch:	0.00259 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.061 lbs [27.67 g]

Cable

Cable Type	RG223
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.209 in [5.31 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]

SMA Male to SMA Male Cable Using RG223 Coax with HeatShrink, LF Solder



PE3377LF/HS

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMA Male
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	50 µin minimum	50 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	100 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 µin minimum	100 µin minimum
Hex Size	5/16 inch	5/16 inch
Torque	3 in-lbs 0.34 Nm	3 in-lbs 0.34 Nm

Environmental Specifications

Operating Range Temperature -40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Male to SMA Male Cable Using RG223 Coax with HeatShrink, LF Solder



PE3377LF/HS

Typical Performance Data

How to Order

Part Number Configuration:

PE3377LF/HS - xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: PE3377LF/HS-12 = 12 inches long cable
PE3377LF/HS-100cm = 100 cm long cable

SMA Male to SMA Male Cable Using RG223 Coax with HeatShrink, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Cable Using RG223 Coax with HeatShrink, LF Solder PE3377LF/HS](#)

URL: <https://www.pasternack.com/sma-male-to-sma-male-cable-using-rg223-with-heatshrink-lf-solder-pe3377lf-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

SMA Male to SMA Male Cable Using RG223 Coax with HeatShrink, LF Solder

