COMPONENTS	IMPEDANCE	Standard Lengths
MALE NC MALE	75 OHM 75 OHM	-12 12"
G179B/U	75 OHM	-24 24"
		-36 36"
		-48 48"
		-60 60"
		-XXX Custom Length in incl
		LENGTH MEASURED FROM
		CONTACT TO CONTACT
.800ø		
75 0	DHM	75 OHM
N M.	ALE	BNC MALE
		PASTERNACK ENTERPRISES,
		P.O BOX 16759, IRVINE, CA 92623 PHONE (949) 261-1920 FAX (949) 261-
		WEB ADDRESS: www.pasternack.cd E-MAIL ADDRESS: sales@pasternack
		ESTABLISHED 1972
		DWG TITLE DES. CABLE ASSEMBLY, RG179B/U, 75 OHM
		PE3398LF-XX MALE TO 75 OHM BNC MALE (LEAD FR
		ROHS 2002/95/EC REV. A FSCM NO. 53919 CAD FILE 021308 SCALE N/A SIZE A
		RoHS Compliance A ALL SECUCIONS ARE NOMINAL.
		Certified 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIM 3. DIMENSIONS ARE IN INCHES.
		4. LENGTH TOLERANCE IS ± 1.5% OR ±3/8", WHICHEVER IS GREATER.