
COMPONENTS	IMPEDANCE
SMA MALE	50 OHM
SMA MALE RIGHT ANGLE	50 OHM
RG223/U	50 OHM

Standard Lengths		
-12	12"	
-24	24"	
-36	36"	
-48	48"	
-60	60"	
-xx	Custom Length in inches	





PASTERNACK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE **PE3429-XX** DES. CABLE ASSEMBLY, RG223/U, SMA MALE TO SMA MALE RIGHT ANGLE

FSCM NO. 53919 SIZE A

CAD FILE 010707

SCALE N/A 127

NOTES:

- 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
- 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
- 3. DIMENSIONS ARE IN INCHES.
- 4. LENGTH TOLERANCE IS ± 1.5% OR ±3/8", WHICHEVER IS GREATER