


COMPONENTS	IMPEDANCE
NMO MOUNT	50 OHM
TNC FEMALE	50 OHM
RG58	50 OHM

Standard Lengths	
-60	60"
-120	120"
-180	180"
-xxx	Custom Length in inches



PASTERNACK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE37849-XX

DES.

ANTENNA MOUNT (NMO) CABLE ASSEMBLY,
NMO MOUNT TO TNC FEMALE, 1GHz, RG58

SIZE A

FSCM NO. 53919

CAD FILE 011607

SCALE N/A

127

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES.
4. LENGTH TOLERANCE IS $\pm 1.5\%$ OR $\pm 3/8"$, WHICHEVER IS GREATER