


| COMPONENTS | IMPEDANCE |
|------------|-----------|
| N MALE | 50 OHM |
| N MALE | 50 OHM |
| PE-C240 | 50 OHM |
| | |

| Standard Lengths | |
|------------------|-------------------------|
| -36 | 36" |
| -48 | 48" |
| -60 | 60" |
| -72 | 72" |
| -120 | 120" |
| -XXX | Custom Length in Inches |
| | |



PASTERNACK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
 E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE37941-XX

DES. CABLE ASSEMBLY, PE-C240, N MALE TO N MALE

| | | | | | |
|--------|----------------|-----------------|-----------|--------|------|
| REV. C | FSCM NO. 53919 | CAD FILE 122211 | SCALE N/A | SIZE A | 2233 |
|--------|----------------|-----------------|-----------|--------|------|

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES.
4. LENGTH TOLERANCE IS $\pm 1.5\%$ OR $3/8"$, WHICHEVER IS GREATER.