



How To Order		Part # Ext.	Length In Inches
<b>Part Number Configuration</b> PE3 <span style="border: 1px solid black; padding: 2px;">zzz</span> <span style="border: 1px solid black; padding: 2px;">yy</span> - <span style="border: 1px solid black; padding: 2px;">xx</span> <span style="border: 1px solid black; padding: 2px;">uu</span> 00 - 99999 LF = Lead Free < Blank > = Standard Note: LF applies only to RF cables CM = Centimeters < Blank > = Inches Length	<b>Examples</b>	<b>-12</b>	<b>12"</b>
	PE3000LF-100	<b>-24</b>	<b>24"</b>
	PE3000-100	<b>-36</b>	<b>36"</b>
	PE3000LF-100CM	<b>-48</b>	<b>48"</b>
	PE3000-100CM	<b>-60</b>	<b>60"</b>
		<b>-xx</b>	<b>Custom Length</b>
Components		Impedance	Length In Centimeters
<b>N MALE</b>	<b>50 OHM</b>	<b>-25CM</b>	<b>25Cm</b>
<b>N FEMALE</b>	<b>50 OHM</b>	<b>-50CM</b>	<b>50Cm</b>
<b>PE-C600</b>	<b>50 OHM</b>	<b>-75CM</b>	<b>75Cm</b>
-	-	<b>-100CM</b>	<b>100Cm</b>
		<b>-125CM</b>	<b>125Cm</b>
		<b>-xxCM</b>	<b>Custom Length</b>

**PASTERNAK ENTERPRISES, INC.**

P.O BOX 16759, IRVINE, CA 92623  
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: [www.pasternack.com](http://www.pasternack.com)  
 E-MAIL ADDRESS: [sales@pasternack.com](mailto:sales@pasternack.com)  
**COAXIAL & FIBER OPTICS**

**PASTERNAK ENTERPRISES®**  
ESTABLISHED 1972

DWG TITLE	PE37951		DES.	CABLE ASSEMBLY, PE-C600, N MALE TO N FEMALE	
REV. C	FSCM NO. 53919	CAD FILE	032912	SCALE	N/A
		SIZE	A	2233	

**NOTES:**  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES [mm].  
 4. LENGTH TOLERANCE IS ± 1.5% OR 3/8", WHICHEVER IS GREATER.