



How To Order

Part Number Configuration

PE3 zzz yy - xx uu

00 - 99999

LF = Lead Free
< Blank > = Standard

CM = Centimeters
< Blank > = Inches

Note: LF applies only to RF cables

Length

Examples

PE3000LF-100

PE3000-100

PE3000LF-100CM

PE3000-100CM

Part # Ext.	Length In Inches
-12	12"
-24	24"
-36	36"
-48	48"
-60	60"
-xx	Custom Length
Part # Ext.	Length In Centimeters



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

Components	Impedance
7/16 DIN MALE	50 OHM
7/16 DIN MALE RIGHT ANGLE	50 OHM
PC-C400	50 OHM
-	-

-25CM	25Cm
-50CM	50Cm
-75CM	75Cm
-100CM	100Cm
-125CM	125Cm
-xxCM	Custom Length

DWG TITLE
PE37958

DES. CABLE ASSEMBLY, PE-C400, 7/16 DIN MALE TO 7/16 DIN MALE RIGHT ANGLE

REV. D	FSCM NO. 53919	CAD FILE 032912	SCALE N/A	SIZE A	2233
--------	----------------	-----------------	-----------	--------	------

- NOTES:**
- UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 - ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 - DIMENSIONS ARE IN INCHES [mm].
 - LENGTH TOLERANCE IS ± 1.5% OR 3/8", WHICHEVER IS GREATER.