
COMPONENTS	IMPEDANCE
SMA MALE RIGHT ANGLE	50 OHM
BNC MALE	50 OHM
PE-T195*	50 OHM

	Standard Lengths	
-12	12"	
-24	24"	
-36	36"	
-48	48"	
-60	60"	
-XXX	Custom Lenth in Inches	





PASTERNACK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE PE38093-XX DES. CABLE ASSEMBLY, PE-T195*, SMA MALE RIGHT ANGLE TO BNC MALE

FSCM NO. 53919 REV.

NOTES:

CAD FILE 041609

SCALE N/A

SIZE A 127

- 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES.
- 4. LENGTH TOLERANCE IS ± 1.5% OR 3/8", WHICHEVER IS GREATER.

* PE-T Series is a functionally equivalent to Times Microwave LMR® series

** LMR[®] is a registered trademark of Times Microwave