

SMA Male to N Female Bulkhead Semi-Flexible Precision Cable Using PE-SR402FLJ Coax, RoHS



TECHNICAL DATA SHEET

PE39469

Pasternack's formable cable assemblies are hand formable semi-rigid replacements that are an alternative to costly preformed assemblies. The formable semi-rigid cable alternatives are dimensionally and electrically similar to their semi-rigid counterpart and have a tinned-copper-braid outer shield that provides excellent RF shielding. The hand formable cable assemblies from Pasternack do not require special tooling to shape or reshape the assemblies and can replace standard semi-rigid versions. The assemblies are available with or without a FEP jacket and are RoHS compliant,

Features

- Dimensionally and electrically the same as standard, solid outer conductor semi-rigid coax
- Cable may be formed by hand and does not require special tools to bend
- May be formed more than once without damaging the outer conductor
- High RF Shielding >100 dB
- 100% Hi-pot and continuity tested
- 100% VSWR tested to max frequency of assembly
- Standard and custom lengths ship the same day

Configuration

Connector 1 Connector 2

Cable Type

SMA Male

N Female Bulkhead PE-SR402FLJ

Electrical Specifications

Frequency Range Impedance

Velocity of Propagation

Group Delay

RF Shielding

DC to 11 GHz 50 Ohms

70 %

1.43 ns/ft [4.69 ns/m]

100 dB

Performance by Frequency

Frequency 1

Frequency

Insertion Loss

500 MHz

0.279 dB/ft [0.92 dB/m]

Frequency 2

Frequency

Insertion Loss

1000 MHz

0.319 dB/ft [1.05 dB/m]

Frequency 3

Frequency

Insertion Loss

2.5 GHz

0.379 dB/ft [1.24 dB/m]

Frequency 4

Frequency

Insertion Loss

5 GHz

0.48 dB/ft [1.57 dB/m]

Frequency 5

Frequency

11 GHz

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to N Female Bulkhead Semi-Flexible Precision Cable Using PE-SR402FLJ Coax, RoHS PE39469

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



SMA Male to N Female Bulkhead Semi-Flexible Precision Cable Using PE-SR402FLJ Coax, RoHS



TECHNICAL DATA SHEET

PE39469

Insertion Loss 0.643 dB/ft [2.11 dB/m]

Mechanical Specifications

Size

Diameter 0.866 in [22 mm]

Cable Color Black

One Time Minimum Bend Radius 0.315 in [8 mm]
Repeated Minimum Bend Radius 1.575 in [40.01 mm]

Cable

Cable Type PE-SR402FLJ

Inner Conductor Type Solid

Cable Inner Conductor Copper Clad Steel, Silver

No of Shields 1
Dielectric Type PTFE
Jacket Material FEP

Jacket Diameter 0.161 in [4.09 mm]

Connector 1

Type SMA Male Configuration Straight

Coupling Nut Material and Plating Passivated Stainless Steel

 Hex Size
 5/16 in.

 Torque
 8 in-lbs [0.9 Nm]

Body Material and Plating Brass, Gold

Connector 2

Type N Female Bulkhead

Configuration Straight Mount Method Bulkhead

Inner Conductor Material and Plating Phosphor Bronze, Gold

Body Material and Plating Brass, Nickel Dielectric Type PTFE

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant Yes
REACH Compliant 12/15/2010

Plotted and Other Data

Notes:


• Values at +25 °C, sea level

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to N Female Bulkhead Semi-Flexible Precision Cable Using PE-SR402FLJ Coax, RoHS PE39469

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com








TECHNICAL DATA SHEET

PE39469

How to Order



Example: PE39469-12 = 12 inches long cable

PE39469-100cm = 100 cm long cable

SMA Male to N Female Bulkhead Semi-Flexible Precision Cable Using PE-SR402FLJ Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to N Female Bulkhead Semi-Flexible Precision Cable Using PE-SR402FLJ Coax, RoHS PE39469


URL: http://www.pasternack.com/sma-male-n-female-pe-sr402flj-cable-assembly-pe39469-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE39469 CAD DrawingSMA Male to N Female Bulkhead Semi-Flexible Precision Cable Using PE-SR402FLJ Coax, RoHS



Note: This part is lead free.

