



SSMC Plug to TNC Female Bulkhead Cable Using RG188 Coax

RF Cable Assemblies Technical Data Sheet

PE3C7651

Configuration

- Connector 1: SSMC Plug
- Connector 2: TNC Female Bulkhead
- Cable Type: RG188

Features

- Max Frequency 3 GHz
- PTFE Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C7651 SSMC plug to TNC female bulkhead cable using RG188 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SSMC to TNC cable assembly has a plug to female gender configuration with 50 ohm flexible RG188 coax. The PE3C7651 SSMC plug to TNC female cable assembly operates to 3 GHz. Our RF cable assembly with TNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	400					MHz
Insertion Loss (Typ.)	0.2					dB/ft
	0.66					dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SSMC Plug to TNC Female Bulkhead Cable Using RG188 Coax PE3C7651](#)



SSMC Plug to TNC Female Bulkhead Cable Using RG188 Coax

RF Cable Assemblies Technical Data Sheet

PE3C7651

Mechanical Specifications

Cable Assembly

Weight 0.054 lbs [24.49 g]

Cable

Cable Type RG188
Impedance 50 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper Clad Steel, Silver
Dielectric Type PTFE
Number of Shields 1
Shield Layer 1 Silver Plated Copper Braid
Jacket Material PTFE, White
Jacket Diameter 0.11 in [2.79 mm]

Connectors

Description	Connector 1	Connector 2
Type	SSMC Plug	TNC Female Bulkhead
Specification		MIL-STD-348
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	
Contact Material and Plating	Beryllium Copper, Gold	Brass, Gold
Contact Plating Specification		30 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Beryllium Copper, Gold	Brass, Nickel
Coupling Nut Material and Plating	Beryllium Copper, Gold	
Hex Size	5/32 inch	
Torque	1 in-lbs [0.11 Nm]	

Environmental Specifications

Temperature

Operating Range -45 to +120 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SSMC Plug to TNC Female Bulkhead Cable Using RG188 Coax PE3C7651](#)



SSMC Plug to TNC Female Bulkhead Cable Using RG188 Coax

RF Cable Assemblies Technical Data Sheet

PE3C7651

How to Order

Part Number Configuration:

PE3C7651

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C7651-12 = 12 inches long cable
PE3C7651-100cm = 100 cm long cable

SSMC Plug to TNC Female Bulkhead Cable Using RG188 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SSMC Plug to TNC Female Bulkhead Cable Using RG188 Coax PE3C7651](https://www.pasternack.com/ssmc-plug-to-tnc-female-bulkhead-cable-using-rg188-pe3c7651-p.aspx)

URL: <https://www.pasternack.com/ssmc-plug-to-tnc-female-bulkhead-cable-using-rg188-pe3c7651-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C7651 CAD Drawing
SSMC Plug to TNC Female Bulkhead Cable Using RG188 Coax

