

Reverse Polarity SMA Plug to TNC Male Cable Using RG316 Coax, LF Solder




PE3C8566LF

Configuration

- Connector 1: SMA Plug Reverse Polarity
- Connector 2: TNC Male
- Cable Type: RG316
- Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- 69% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C8566LF reverse polarity SMA plug to TNC male cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack reverse polarity SMA to TNC cable assembly has a plug to male gender configuration with 50 ohm flexible RG316 coax. The PE3C8566LF reverse polarity SMA plug to TNC male cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR		1.4:1		
Velocity of Propagation		69		%
Dielectric Withstanding Voltage (AC)			750	Vrms
Jacket Spark			2,000	Vrms

Specifications by Frequency

Reverse Polarity SMA Plug to TNC Male Cable Using RG316 Coax, LF Solder



PE3C8566LF

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	100	250	500	1000	3000	MHz	
PE3C8566LF	Custom Lengths Available	Insertion Loss (Typ.)	0.11	0.16	0.238	0.38	0.58	dB/ft	
			0.37	0.53	0.79	1.25	1.91	dB/m	
PE3C8566LF-12	12 inch	Insertion Loss (Typ.)	0.25	0.31	0.41	0.58	0.86	dB	0.061
PE3C8566LF-24	24 inch	Insertion Loss (Typ.)	0.36	0.47	0.65	0.96	1.44	dB	0.072
PE3C8566LF-36	36 inch	Insertion Loss (Typ.)	0.47	0.63	0.89	1.34	2.02	dB	0.082
PE3C8566LF-48	48 inch	Insertion Loss (Typ.)	0.58	0.79	1.13	1.72	2.6	dB	0.092
PE3C8566LF-72	72 inch	Insertion Loss (Typ.)	0.8	1.11	1.6	2.48	3.76	dB	0.112

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.1x $\sqrt{\text{fGHz}}$ dB
Base Weight:	0.061 pounds
Additional Weight per Inch:	0.00084 pounds

Mechanical Specifications

Cable Assembly

Weight	0.061 lbs [27.67 g]
--------	---------------------

Cable

Cable Type	RG316
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.102 in [2.59 mm]

Reverse Polarity SMA Plug to TNC Male Cable Using RG316 Coax, LF Solder



PE3C8566LF

Connectors

Description	Connector 1	Connector 2
Type	SMA Plug Reverse Polarity	TNC Male
Specification	MIL-STD-348	
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Gold	Beryllium Copper, Gold
Contact Plating Specification	MIL-G-45204	15 µin minimum
Dielectric Type	PTFE	Teflon
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	QQ-N-290	100 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	QQ-N-290	100 µin minimum
Hex Size	5/16 inch	
Torque	3 in-lbs 0.34 Nm	

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Reverse Polarity SMA Plug to TNC Male Cable Using RG316 Coax, LF Solder



PE3C8566LF

Typical Performance Data

How to Order

Part Number Configuration:

PE3C8566LF **- xx** **uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE3C8566LF-12 = 12 inches long cable
 PE3C8566LF-100cm = 100 cm long cable

Reverse Polarity SMA Plug to TNC Male Cable Using RG316 Coax, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Plug to TNC Male Cable Using RG316 Coax, LF Solder PE3C8566LF](#)

URL: <https://www.pasternack.com/reverse-polarity-sma-plug-to-tnc-male-cable-using-rg316-lf-solder-pe3c8566lf-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C8566LF CAD Drawing

Reverse Polarity SMA Plug to TNC Male Cable Using RG316 Coax, LF Solder

