


Fiber Optic Patch Cable, Simplex FC APC, NK to FC APC, NK, SM OS2, 2.0mm PVC, Yellow-10M



PE3FCA131-10M

Features

- Single mode OS2 indoor fiber optic cable assembly
- Simplex FC APC, narrow key to FC APC, narrow key
- Indoor PVC cable
- Suitable for general purpose areas
- Custom lengths available with the same fast delivery

Applications

- Telecom & Networking
- Data Centers
- Fiber Optic Test & Measurement
- Medical & Biomedical
- Military & Defense
- Industrial Automation & Sensing
- Scientific Research & High-Precision Optical Systems

Description

The PE3FCA131-10M fiber optic patch cord is a robust and versatile fiber optic cable assembly from Pasternack designed for high-performance data transmission in various environments. Equipped with Simplex FC APC, narrow key to FC APC, narrow key connectors, this simplex OS2 Single Mode fiber optic patch cable is optimized for indoor use, utilizing a PVC cable. The FC connectors are narrow key with of 1.95mm-2.05mm, ensuring optimum connectivity. The 2.0mm diameter construction, combined with its Yellow color, makes it easy to identify in complex setups, while its operating temperature range of 0°C to 60°C and storage temperature of -20°C to 60°C provides reliable performance across diverse conditions.

The Pasternack PE3FCA131-10M fiber optic jumper is ideal for applications where reliable, precision connectivity is critical. The Single Mode design of the OS2 fiber offers stable, high-speed transmission, making it suitable for Telecom & Networking, Data Centers, and Fiber Optic Test & Measurement. With the flexibility of custom lengths, Pasternack's PE3FCA131-10M fiber optic assembly can be tailored to meet specific installation requirements, ensuring efficient network management in high-density, fiber setups without compromising on delivery time or quality.

Beyond networking, the Pasternack PE3FCA131-10M fiber patch cord supports an array of industry applications, from Military & Defense to Scientific Research & High-Precision Optical Systems. This fiber assembly offers a reliable and durable solution for any setting requiring high-quality data transmission in a controlled, indoor environment. For further information on similar fiber optic products, our expert technical support and trained sales team can get you the ideal fiber optic simplex cable assembly as per your requirements.


Configuration

Function	Patch
Cable Type	Simplex Single Mode
Mode	Single Mode
Mode Class	OS2
Fiber Diameter	9/125 um
Connection 1 Type	FC
Connection 1 Polish	APC
Connection 2 Type	FC
Connection 2 Polish	APC
Cable Color	Yellow

Optical Specifications

Description	Minimum	Typical	Maximum	Units
Return Loss	60			dB

Fiber Optic Patch Cable, Simplex FC APC, NK to FC
APC, NK, SM OS2, 2.0mm PVC, Yellow-10M



PE3FCA131-10M

Optical Specifications

Description	Minimum	Typical	Maximum	Units
Insertion Loss			0.3	dB

Mechanical Specifications

Cable Assembly

Length	10 m [393.70 in]
Width/Diameter	2 mm
Weight	1.45 kg [3.2 lbs]

Cable

Cable Type	Patch
Static Bend Radius	15 mm
Dynamic Bend Radius	30 mm
Max Crush Resistance, Short Term (N/100mm)	200
Max Crush Resistance, Long Term (N/100mm)	50

Connectors

Description	Connector 1	Connector 2
Type	FC	FC
Specification	Key width of 1.95mm-2.05mm	Key width of 1.95mm-2.05mm
Connector Polish	APC	APC

Environmental Specifications


Operating Range Temperature	0 to +60 deg C
Storage Range Temperature	-20 to +60 deg C
Ingress Protection (IP) Rating	Non-Rated

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Fiber Optic Patch Cable, Simplex FC APC, NK to FC APC, NK, SM OS2, 2.0mm PVC, Yellow-10M



PE3FCA131-10M

Typical Performance Data

How to Order

Part Number Configuration:

PE3FCA131

- xx

uu

Unit of Measure:

M = Meters

<blank> = Inches

Length

Base Number

Example: PE3FCA131-12 = 12 inches long cable
PE3FCA131-100cm = 100 cm long cable

Fiber Optic Patch Cable, Simplex FC APC, NK to FC APC, NK, SM OS2, 2.0mm PVC, Yellow-10M from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Fiber Optic Patch Cable, Simplex FC APC, NK to FC APC, NK, SM OS2, 2.0mm PVC, Yellow-10M PE3FCA131-10M](#)

URL: <https://www.pasternack.com/fc-fc-single-mode-apc-fiber-optic-cable-assembly-pe3fca131-10m-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3FCA131-10M CAD Drawing
Fiber Optic Patch Cable, Simplex FC APC, NK to FC APC, NK, SM OS2, 2.0mm PVC, Yellow-10M

