

## Fiber Optic Patch Cable, Duplex FC APC, NK to FC APC, NK, SM OS2, 2.0mm Riser, Yellow-10M



### PE3FCA505-10M

#### Features

- Single Mode OS2 indoor fiber optic cable assembly
- Dual FC APC to Dual FC APC
- Indoor Riser (OFNR) cable
- Suitable for ceilings and riser areas
- 2.0mm x 4.1mm duplex zip-cord
- Custom lengths available with the same fast delivery

#### Applications

- Telecom & Networking
- Data Centers
- Fiber Optic Test & Measurement
- Medical & Biomedical
- Military & Defense
- Industrial Automation & Sensing
- Scientific Research & High-Precision Optical Systems

#### Description

The PE3FCA505-10M fiber optic patch cord from Pasternack is a robust and versatile fiber optic cable assembly designed for high-performance data transmission in various environments. Equipped with Dual FC APC to Dual FC APC connectors, this duplex OS2 Single Mode fiber optic patch cable is optimized for indoor use, featuring a Riser (OFNR) that ensures compliance with fire and safety standards. The 2.0mm x 4.1mm diameter construction, combined with its yellow color, makes it easy to identify in complex setups, while its operating temperature range of -20°C to 70°C and storage temperature of -40°C to 70°C provides reliable performance across diverse conditions.

Pasternack's PE3FCA505-10M fiber optic jumper is ideal for applications where reliable, long-range data connectivity is critical. The single mode design of the OS2 fiber offers stable, high-speed transmission over long distances, making it suitable for Telecom & Networking, Data Centers, and Corporate Networks. With the flexibility of custom lengths, the Pasternack PE3FCA505-10M fiber optic assembly can be tailored to meet specific installation requirements, ensuring efficient network management in high-density setups without compromising on delivery time or quality.

Beyond networking, the Pasternack PE3FCA505-10M fiber patch cord supports an array of industry applications, from Broadcasting & Media Production and Military & Defense to Healthcare & Medical Imaging. This fiber assembly offers a reliable and durable solution for any setting requiring high-quality data transmission in a controlled, indoor environment. For further information on similar fiber optic products, our expert technical support and trained sales team can get you the ideal fiber optic duplex cable assembly as per your requirements.

#### Configuration

|                     |                    |
|---------------------|--------------------|
| Function            | Patch              |
| Cable Type          | Duplex Single Mode |
| Mode                | Single Mode        |
| Mode Class          | OS2                |
| Fiber Diameter      | 9/125 um           |
| Connection 1 Type   | FC                 |
| Connection 1 Polish | APC                |
| Connection 2 Type   | FC                 |
| Connection 2 Polish | APC                |
| Cable Color         | Yellow             |

#### Mechanical Specifications

##### Cable Assembly

|                |                     |
|----------------|---------------------|
| Length         | 10 m [393.70 in]    |
| Width/Diameter | 2 mm                |
| Weight         | 39.01 g [0.086 lbs] |

Fiber Optic Patch Cable, Duplex FC APC, NK to FC  
APC, NK, SM OS2, 2.0mm Riser, Yellow-10M



## PE3FCA505-10M

### Cable

|                                            |       |
|--------------------------------------------|-------|
| Cable Type                                 | Patch |
| Static Bend Radius                         | 15 mm |
| Dynamic Bend Radius                        | 30 mm |
| Max Crush Resistance, Short Term (N/100mm) | 300   |
| Max Crush Resistance, Long Term (N/100mm)  | 100   |

### Connectors

| Description      | Connector 1               | Connector 2               |
|------------------|---------------------------|---------------------------|
| Type             | FC                        | FC                        |
| Specification    | Key with of 1.95mm-2.05mm | Key with of 1.95mm-2.05mm |
| Connector Polish | APC                       | APC                       |

### Environmental Specifications

|                                |                  |
|--------------------------------|------------------|
| Operating Range Temperature    | -20 to +70 deg C |
| Storage Range Temperature      | -40 to +70 deg C |
| Ingress Protection (IP) Rating | Non-Rated        |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Fiber Optic Patch Cable, Duplex FC APC, NK to FC APC, NK, SM OS2, 2.0mm Riser, Yellow-10M



## PE3FCA505-10M

### Typical Performance Data

### How to Order

Part Number Configuration: **PE3FCA505 - xx uu**

Unit of Measure:  
M = Meters  
<blank> = Inches

Length

Base Number

Example: PE3FCA505-12 = 12 inches long cable  
PE3FCA505-100cm = 100 cm long cable

Fiber Optic Patch Cable, Duplex FC APC, NK to FC APC, NK, SM OS2, 2.0mm Riser, Yellow-10M from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Fiber Optic Patch Cable, Duplex FC APC, NK to FC APC, NK, SM OS2, 2.0mm Riser, Yellow-10M PE3FCA505-10M](#)

URL: <https://www.pasternack.com/fc-fc-single-mode-9-125-sm-duplex-riser-fiber-patch-cable-fiber-optic-cable-assembly-pe3fca505-10m-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3FCA505-10M CAD Drawing

Fiber Optic Patch Cable, Duplex FC APC, NK to FC APC, NK, SM OS2, 2.0mm Riser, Yellow-10M

