

SMA Male Right Angle to SMB Plug Right Angle Cable 36 Inch Length Using PE-SR405FL Coax



RF Cable Assemblies Technical Data Sheet

PE3W01739-36

Configuration • Connector 1: SMA Male Right Angle Connector 2: SMB Plug Right Angle • Cable Type: PE-SR405FL Features SHIELD Max Frequency 6 GHz • 69.5% Phase Velocity 0.086 DIELECTRIC Ø [2.2] SOLID CENTER CONDUCTOR Applications General Purpose Laboratory Use

Description

Pasternack's PE3W01739-36 SMA male right angle to SMB plug right angle 36 inch cable using PE-SR405FL coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack SMA to SMB cable assembly has a male to plug gender configuration with 50 ohm formable PE-SR405FL coax. The PE3W01739-36 SMA male to SMB plug cable assembly operates to 6 GHz. The right angle SMA and right angle SMB interfaces on the PE-SR405FL cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Conductor		65.7 [215.55]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		10.2 [33.46]		Ω/1000ft [Ω/Km]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male Right Angle to SMB Plug Right Angle Cable 36 Inch Length Using PE-SR405FL Coax PE3W01739-36

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

© 2018 Pasternack Enterprises All Rights Reserved



SMA Male Right Angle to SMB Plug Right Angle Cable 36 Inch Length Using PE-SR405FL Coax



RF Cable Assemblies Technical Data Sheet

PE3W01739-36

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2	4	6	GHz
Insertion Loss (Typ.)	0.85	1.08	1.32	1.8	2.2	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.4dB of connector loss.

Mechanical Specifications

Cable Assembly Length* Diameter

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 36 in [914.4 mm] 0.315 in [8 mm]

PE-SR405FL 50 Ohms Solid Copper Clad Steel, Silver PTFE 1 Tinned Copper Braid

Connectors

Description	Connector 1	Connector 2	
Туре	SMA Male Right Angle	SMB Plug Right Angle	
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating	Brass, Gold	Gold	
Contact Plating Specification	2µ in. minimum		
Dielectric Type	PTFE	PTFE	
Body Material and Plating	Brass, Gold	Brass, Gold	
Body Plating Specification	1µ in. minimum		
Coupling Nut Material and Plating	Passivated Stainless Steel		
Hex Size	5/16 in.		
Torque	8 in-lbs [0.9 Nm]		

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male Right Angle to SMB Plug Right Angle Cable 36 Inch Length Using PE-SR405FL Coax PE3W01739-36

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

© 2018 Pasternack Enterprises All Rights Reserved



SMA Male Right Angle to SMB Plug Right Angle Cable 36 Inch Length Using PE-SR405FL Coax


RF Cable Assemblies Technical Data Sheet

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male Right Angle to SMB Plug Right Angle Cable 36 Inch Length Using PE-SR405FL Coax PE3W01739-36

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

© 2018 Pasternack Enterprises All Rights Reserved










SMA Male Right Angle to SMB Plug Right Angle Cable 36 Inch Length Using PE-SR405FL Coax



RF Cable Assemblies Technical Data Sheet

PE3W01739-36



Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com PE3W01739-36 CAD Drawing SMA Male Right Angle to SMB Plug Right Angle Cable

MA Male Right Angle to SMB Plug Right Angle Cat 36 Inch Length Using PE-SR405FL Coax

