

QN Female Bulkhead Connector Crimp/Solder Attachment For RG213, RG215, .500 inch Diameter

TECHNICAL DATA SHEET



PE44607

Configuration	
Connector	QN Female
Connector Interface Type Cable Attachment Method (Shield/Contact)	RG213,RG215 Crimp/Solder
Mount Method	Bulkhead
Electrical Specifications	
Frequency Range, GHz	DC to 11
Impedance, Ohms	50
Maximum Return Loss, dB	0.17
Maximum Operating Voltage, Volts	1,000
Dielectric Withstanding Voltage, Vrms	2,500
Frequency 1	
Frequency, MHz	DC to 1,000
Return Loss, dB	33
Insertion Loss, dB	0.05
Frequency 2	
Frequency, GHz	1 to 2.5
Return Loss, dB	31
Insertion Loss, dB	0.08
Frequency 3	
Frequency, GHz	2.5 to 6
Return Loss, dB	22
Insertion Loss, dB	0.12
Aechanical Specifications	
Temperature	
Operating Range, deg C	-40 to +125
Size	
Length, in [mm]	1.68 [42.67]
Width/Dia., in [mm]	0.67 [17.02]
Weight, lbs [g]	0.096 [43.54]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: QN Female Bulkhead Connector Crimp/Solder Attachment For RG213, RG215, .500 inch Diameter PE44607

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



QN Female Bulkhead Connector Crimp/Solder Attachment For RG213, RG215, .500 inch Diameter



PE44607

Type Mating Cycles Contact Material and Plating Contact Plating Specification Body Material and Plating Dielectric Type QN Female 100 Spring Bronze, Gold 6µ in. minimum Brass, Tri-Metal PTFE

Compliance Certifications (visit www.Pasternack.com for current document) RoHS Compliant Yes

Plotted and Other Data

Notes:

TECHNICAL DATA SHEET

Connector

Values at 25 °C, sea level

QN Female Bulkhead Connector Crimp/Solder Attachment For RG213, RG215, .500 inch Diameter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: QN Female Bulkhead Connector Crimp/Solder Attachment For RG213, RG215, .500 inch Diameter PE44607

URL: http://www.pasternack.com/qn-female-standard-rg213-rg215-connector-pe44607-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com PE44607 CAD Drawing

QN Female Bulkhead Connector Crimp/Solder Attachment

For RG213, RG215, .500 inch Diameter

