

SMA Female Bulkhead Mount Connector, .068 inch  
End Launch PCB, .236 inch D Hole, IP67 mated



**PE517835**

**Configuration**

- SMA Female Connector
- MIL-STD-348B
- 50 Ohms
- Straight Body Geometry
- Bulkhead

**Features**

- Max. Operating Frequency 18 GHz
- Gold over Nickel over Copper Plated Beryllium Copper Contact
- IP67 Mated

**Applications**

- General Purpose Test
- Rack and Panel Mount Applications
- PCB Applications

**Description**

Pasternack's PE517835 SMA Female Bulkhead Mount Connector PCB Mount Attachment IP67 Mated Mated is part of our full line of RF components available for same-day shipping. Our SMA female connector operates up to a maximum frequency of 18 GHz. This SMA bulkhead connector allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The connector has an IP67 rating to protect against dust and temporary moisture protection under immersion conditions.

Our SMA female bulkhead connector PE517835 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR		1.2:1		
Dielectric Withstanding Voltage (AC)			1,500	Vrms
High Potential Voltage			500	Vrms
Inner Conductor DC Resistance			3	mOhms
Outer Conductor DC Resistance			2	mOhms
Insulation Resistance	5,000			MOhms
Impedance		50		Ohms

Electrical Specification Notes:  
Insertion loss is equal to  $0.04 \times \text{SQRT } F(\text{GHz})$  dB

**Mechanical Specifications**

Size	
Length	0.689 in [17.5 mm]
Width	0.433 in [11 mm]
Height	0.433 in [11 mm]

SMA Female Bulkhead Mount Connector, .068 inch  
End Launch PCB, .236 inch D Hole, IP67 mated



**PE517835**

Weight	0.007 lbs [3.18 g]
Mating Cycles	100 Cycles
Mating Torque	4 to 5.3 in-lbs [[0.45 to 0.60 Nm]]
Cable Retention Force	6.1 lbs [2.77 kg]

**Material Specifications**

Description	Material	Plating
Contact	Beryllium Copper	Gold over Nickel over Copper
Insulation	PTFE	
Body	Brass	Gold over Nickel over Copper
Gasket	Silicone	

**Environmental Specifications**

<b>Temperature</b>	
Operating Range	-65 to +165 deg C
Ingress Protection (IP) Rating	IP67 Mated
Humidity	MIL-STD-202, Method 106
Thermal Shock	MIL-STD-202, Method 107, Condition B

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

SMA Female Bulkhead Mount Connector, .068 inch End Launch PCB, .236 inch D Hole, IP67 mated from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female Bulkhead Mount Connector, .068 inch End Launch PCB, .236 inch D Hole, IP67 mated PE517835](#)

URL: <https://www.pasternack.com/sma-female-pcb-connector-pe517835.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE517835 CAD Drawing

SMA Female Bulkhead Mount Connector, .068 inch End Launch PCB, .236 inch D Hole, IP67 mated

