



Crimp Tool Kit with .042", .043", .068", .078", .100", .128", .137", .151", .178", .213", .255", .256", .429" Hex Sizes

Crimp Tools Technical Data Sheet

PE5224

Features

- Quick change interchangeable ratchet crimper
- Includes die-set

Configuration

Tool Type	Crimp Tool Kit
Hex Size, Inch	.042", .043", .068", .078", .100", .128", .137", .151", .178", .213", .255", .256", .429"

Mechanical Specifications

Size	
Length	11.61 in [294.89 mm]
Width	2.76 in [70 mm]
Height	8.46 in [214.88 mm]
Weight	1.396 lbs [633.21 g]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

- Notes:
- Values at +25 °C, sea level

Crimp Tool Kit with .042", .043", .068", .078", .100", .128", .137", .151", .178", .213", .255", .256", .429" Hex Sizes from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Crimp Tool Kit with .042", .043", .068", .078", .100", .128", .137", .151", .178", .213", .255", .256", .429" Hex Sizes PE5224](#)

URL: <https://www.pasternack.com/crimp-tool-kit-hex-bit-pe5224-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE5224 CAD Drawing

F Crimp Tool Kit with .042", .043", .068", .078", .100", .128", .137", .151", .178", .213", .255", .256", .429" Hex Sizes A

1 2 3 4 5 6

ZONE		REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
		A	INITIAL RELEASE	03/24/2023	HBAKKE	AGANWANI

TOOL KIT CONTENTS:

QUANTITY	DESCRIPTION
1	QUICK CHANGE INTERCHANGEABLE RATCHET CRIMPER
1	VARIOUS SPECIFIC INTERCHANGEABLE DIE SETS

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X = ±.2 [.5] FRACTIONS
 .XX = ±.02 [.5] ± 1/32
 .XXX = ±.005 [.13] ANGLES ± 1°


CABLE LENGTH TOLERANCES:

≤12 [305] = +1 [25] / -0
 >12 [305] ≤ 60 [1524] = +2 [51] / -0
 >60 [1524] ≤ 120 [3048] = +4 [102] / -0
 >120 [3048] ≤ 300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.



Website: www.Pasternack.com
 Phone: 1.866.727.8376 | 1.949.261.1920



INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE: NONE

SHEET: 1 OF 1

DESCRIPTION: Tool, Quick Change Die-Set Crimping Tool Kit

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	53919	HBAKKE	PE5224	A

F E D C B A