

2.92mm Female to 2.4mm Female Adapter



RF Adapters Technical Data Sheet

PE91295

Configuration

- 2.92mm Female Connector 1
- 2.4mm Female Connector 2

- 50 Ohm
- Straight Body Geometry

Features

- Max VSWR of 1.15:1 up to 40 GHz
- Contact plating according to MIL-G-45204
- Gold over Nickel Plated Beryllium Copper Contact

Applications

- Allows Connection Between Series
- General Purpose Test

Description

Pasternack's PE91295 2.92mm female to 2.4mm female adapter is part of our full line of RF components available for same-day shipping. The 2.92mm connector mates mechanically with commercially available SMA and 3.5mm connectors. The 2.4mm connector mates mechanically with commercially available 1.85mm (V) connectors. Our 2.92mm to 2.4mm adapter has a female to female gender configuration built of durable stainless steel. PE91295 2.92mm female to 2.4mm female adapter operates to 40 GHz. The Pasternack RF adapter provides excellent VSWR of 1.15:1 maximum.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
VSWR			1.15:1	
Insertion Loss			0.32	dB

Electrical Specification Notes: Insertion Loss = 0.05 * sqrt(fGHz)

Mechanical Specifications

Size

 Length
 0.748 in [19 mm]

 Width
 0.25 in [6.35 mm]

 Weight
 0.0097 lbs [4.4 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2.92mm Female to 2.4mm Female Adapter PE91295

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



2.92mm Female to 2.4mm Female Adapter



RF Adapters Technical Data Sheet

PE91295

Description	Connector 1	Connector 2
Туре	2.92mm Female	2.4mm Female
Polarity	Standard	Standard
Mating Cycles	500	500
Mating Torque	8 in-lbs [0.90 Nm] max	8 in-lbs 0.90 Nm max

Material Specifications

	Connect	Connector 1		Connector 2	
Descriptio	n Material	Plating	Material	Plating	
Туре	2.92mm Female		2.4mm Female		
Contact	Beryllium Copper	Gold over Nickel	Beryllium Copper	Gold over Nickel	
		MIL-G-45204		MIL-G-45204	
Insulation	PEI		PEI		
Outer Conducto	r Passivated Stainless Steel		Passivated Stainless Steel		
		ASTM A380		ASTM A380	
Body	Passivated Stainless Steel		Passivated Stainless Steel		
		ASTM A380		ASTM A380	

Environmental Specifications

Temperature

Operating Range

-55 to +150 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2.92mm Female to 2.4mm Female Adapter PE91295

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451



2.92mm Female to 2.4mm Female Adapter



RF Adapters Technical Data Sheet

PE91295

2.92mm Female to 2.4mm Female Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2.92mm Female to 2.4mm Female Adapter PE91295

URL: https://www.pasternack.com/2.92mm-female-2.4mm-female-straight-adapter-pe91295-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE91295 CAD Drawing 2.92mm Female to 2.4mm Female Adapter

