

Flexible RG223 Coax Cable Double Shielded with Black PVC Jacket

RF Cables Technical Data Sheet

RG223/U-FT

Configuration

- Flexible Cable
- 2 Shield(s)

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz
Impedance		50		Ohms
Velocity of Propagation		66		%
Operating Voltage (AC)			1,900	Vrms
Nominal Capacitance		30.8 [101.05]		pF/ft [pF/m]

Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	0.4	1	3	5	11	GHz
Attenuation, Typ	8.19	13.41	24.81	33.49	54.1	dB/100ft
	26.87	44	81.4	109.88	177.49	dB/100m


Mechanical Specifications

Diameter	0.209 in [5.31 mm]
Weight	0.031 lbs/ft [0.05 kg/m]
Min. Bend Radius (Repeated)	1 in [25.4 mm]

Construction Specifications

Description	Material and Plating	Diameter
Inner Conductor	Copper, Silver, 1 Strand	0.035 in [0.89 mm]
Conductor Type	Solid	
Dielectric	PE	0.116 in [2.95 mm]
First Shield	Silver Plated Copper Braid	[]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Flexible RG223 Coax Cable Double Shielded with Black PVC Jacket RG223/U-FT](#)



Flexible RG223 Coax Cable Double Shielded with Black PVC Jacket

RF Cables Technical Data Sheet

RG223/U-FT

Second Shield	Silver Plated Copper Braid	0.156 in [3.96 mm]
Jacket	PVC, Black	0.209 in [5.31 mm]

Environmental Specifications

Temperature

Operating Range

-40 to 80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Flexible RG223 Coax Cable Double Shielded with Black PVC Jacket from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Flexible RG223 Coax Cable Double Shielded with Black PVC Jacket RG223/U-FT](#)

URL: <https://www.pasternack.com/flexible-0.216-rg223-50-ohm-coax-cable-pvc-jacket-rg223-u-ft-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.