

RG402 Coax Cable (by foot) with Copper Outer Conductor



RG402/U-STR-BULK

Configuration

- Semi-Rigid Cable
- M17/130-RG402

Features

- Frequency range of 34 GHz
- Can be bent and formed into shape
- Low Loss
- Phase Stable

Applications

- Military & Defense
- Cable Assemblies
- Precise cable routing

Description

RG402/U-STR-BULK part number from Pasternack is a RG402 coax cable that is semi-rigid. Pasternack RG402 semi-rigid coax cable is 50 Ohm and has a PTFE dielectric. RG402 coax has a shield count of 1 and the maximum frequency for this Pasternack cable is 33 GHz. RG402 coax cable has an attenuation at 1 GHz of 12 dB and a maximum power of 450 watts at 1 GHz.

Pasternack RG402 coax cables are part of over 40,000 RF, microwave and millimeter wave components. RG402 cables and our other RF parts are available for same day shipping worldwide. Custom RF cable assemblies using RG402 or other coax can be built and shipped same day as well.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		33	GHz
Impedance		50		Ohms
Velocity of Propagation		69.5		%
Dielectric Withstanding Voltage (AC)			5,000	Vrms
Corona Discharge at 60 Hz			1,900	Vrms
Power@ 1GHz			450	Watts

Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	5	10	20	GHz
Attenuation, Typ	8	12	28.5	44	67	dB/100ft
	26.25	39.37	93.5	144.36	219.82	dB/100m
Input Power (CW), Max	600	450	180	120	70	Watts

Mechanical Specifications

Weight	0.032 lbs/ft [0.05 kg/m]
Min. Bend Radius (Repeated)	0.25 in [6.35 mm]

RG402 Coax Cable (by foot) with Copper Outer Conductor



RG402/U-STR-BULK

Construction Specifications

Description	Material and Plating	Diameter
Inner Conductor	Copper Clad Steel, Silver, 1 Strand	0.036 in [0.91 mm]
Conductor Type	Solid	
Dielectric	PTFE	0.118 in [3 mm]
Outer Conductor	Copper	0.141 in [3.5 mm]
Jacket	Tan	

Environmental Specifications

Temperature

Operating Range

-40 to 125 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

RG402 Coax Cable (by foot) with Copper Outer Conductor from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [RG402 Coax Cable \(by foot\) with Copper Outer Conductor RG402/U-STR-BULK](#)


URL: <https://www.pasternack.com/50-ohm-semi-rigid-rg402-copper-tan-rg402-u-str-bulk-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

RG402/U-STR-BULK CAD Drawing

RG402 Coax Cable (by foot) with Copper Outer Conductor

REVISIONS		DATE	APPROVED
REV.	DESCRIPTION		
A	INITIAL RELEASE	03/07/2022	AGANWANI



UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

X = $\pm .2$	[5.08]	FRACTIONS
.XX = $\pm .02$	[.51]	$\pm 1/32$
XXX = $\pm .005$	[.13]	ANGLES $\pm 1^\circ$

CABLE LENGTH (L) TOLERANCES:

L ≤ 12 [305] < L ≤ 60 [1524] = $+1$ [25] / -0
12 [305] < L ≤ 120 [3048] = $+2$ [51] / -0
60 [1524] < L ≤ 120 [3048] = $+4$ [102] / -0
120 [3048] < L ≤ 300 [7620] = $+6$ [152] / -0
300 [7620] < L = $+5\%$ / -1% / -0

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.

THREE-ANGLE PROJECTION



THE INFORMATION AND
DESIGN IN THIS DOCUMENT
ARE THE PROPERTY OF
PASTERNAK ENTERPRISES,
INC. ALL RIGHTS RESERVED.

SHEET	1	OF	1
SCALE	N/A		
SIZE	A	ITEM NO.	RG402/U-STR-BULK
CAGE CODE	DZINN	DRAWN BY	REV.

PASTERNAK
an INFINITE brand

Pasternak Enterprises, Inc.
P.O. Box 16759, Irvine, CA 92623.
Phone: 1 949 261 1920 | 1 888 727 8376
Fax: 1 949 261 7451
Website: www.pasternak.com
E-mail: sales@pasternak.com

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE
WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVISION CONTRARY TO U.S. LAW PROHIBITED.