

## 086 Semi-rigid Coax Cable (by foot) with Copper Outer Conductor



### RG405/U-STR-BULK

#### Configuration

- Semi-Rigid Cable
- 1 Shield(s)

#### Features

#### Applications

- Test and Measurement
- Communication Systems
- Wireless Systems
- Medical Equipment
- RADAR
- Low Loss Applications

#### Description

RG405/U-STR-BULK part number from Pasternack is a 086 Semi-rigid coax cable that is semi-rigid. Pasternack RG405 semi-rigid coax cable is 50 Ohm and has a PTFE dielectric. RG405 coax has a shield count of 1, a RF shielding of -110 dB and the maximum frequency for this Pasternack cable is 40 GHz. RG405 coax cable has an attenuation at 1 GHz of 22 dB and a maximum power of 130 watts at 1 GHz.

Pasternack 086 Semi-rigid coax cables are part of over 40,000 RF, microwave and millimeter wave components. RG405 cables and our other RF parts are available for same day shipping worldwide. Custom RF cable assemblies using RG405 or other coax can be built and shipped same day as well.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
Impedance		50		Ohms
Velocity of Propagation		69.5		%
Shielding Effectiveness	-110			dB
Dielectric Withstanding Voltage (AC)			5,000	Vrms
Nominal Capacitance	29.4 [96.46]			pF/ft [pF/m]
Power@ 1GHz			130	Watts

#### Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	1	10	20			GHz
Attenuation, Max	22	80	120			dB/100ft
	72.18	262.47	393.7			dB/100m

Description	F6	F7	F8	F9	F10	Units
Frequency						GHz

## 086 Semi-rigid Coax Cable (by foot) with Copper Outer Conductor



### RG405/U-STR-BULK

#### Mechanical Specifications

Weight	0.013 lbs/ft [0.02 kg/m]
Min. Bend Radius (Repeated)	0.05 in [1.27 mm]

#### Construction Specifications

Description	Material and Plating	Diameter
Inner Conductor	Copper Clad Steel, Silver, 1 Strand	0.02 in [0.51 mm]
Conductor Type	Solid	
Dielectric	PTFE	0.066 in [1.68 mm]
First Shield		0.086 in [2.18 mm]
Outer Conductor	Copper	0.087 in [2.21 mm]

#### Environmental Specifications

Temperature	
Operating Range	-55 to +125 deg C

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

086 Semi-rigid Coax Cable (by foot) with Copper Outer Conductor from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [086 Semi-rigid Coax Cable \(by foot\) with Copper Outer Conductor RG405/U-STR-BULK](#)

URL: <https://www.pasternack.com/50-ohm-semi-rigid-086-semi-rigid-copper-tan-rg405-u-str-bulk-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# RG405/U-STR-BULK CAD Drawing

086 Semi-rigid Coax Cable (by foot) with Copper Outer Conductor

