

## Hermetic Seal Solder Contact with 0.018" Diameter Full Radius Pin, 0.110" Body Diameter and 0.312" Pin Length



### PE1017-7

#### Applications

- General Purpose Test
- Rack and Panel Mount Applications
- Used in Field Replaceable Connectors
- Allows for Replacement of Damaged Connectors

#### Description

Pasternack's PE1017-7 Hermetic seal solder contact with 0.018" diameter full radius pin, 0.110" body diameter and 0.312" pin length is part of our complete line of Connector Launch Accessories available for same-day shipping. This range of accessories includes Glass bead Transitions, Launch Pin & Dielectric Transitions and Pin/Tab Transitions to Microstrip and Stripline Circuits in conjunction with our line of field replaceable flange connectors. These accessories are designed to be compatible with our line of Field Replaceable Connectors to ensure optimal electrical performance for PCB test applications. They are available in commonly used pin diameters of .009", .012", .015", .018", .020" and .036" and in a variety of lengths and sizes depending on the application.

Our PE1017-7 Hermetic seal solder contact with 0.018" diameter full radius pin, 0.110" body diameter and 0.312" pin length datasheet specifications are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.

#### Mechanical Specifications

##### Dimensions

Pin Length	0 in [0 mm]
Pin Diameter	0 in [0 mm]
Tab Diameter	0 in [0 mm]
Dielectric Length	0.18 in [4.57 mm]
Dielectric Diameter	0.109 in [2.77 mm]
Dielectric Material	Kovar
Conn End Pin Length	0.018 in [0.46 mm]
Weight	0.4 lbs [181.44 g]

#### Compliance Certifications

 (see product page for current document)

#### Plotted and Other Data

Notes:

Hermetic Seal Solder Contact with 0.018" Diameter Full Radius Pin, 0.110" Body Diameter and 0.312" Pin Length from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Hermetic Seal Solder Contact with 0.018" Diameter Full Radius Pin, 0.110" Body Diameter and 0.312" Pin Length PE1017-7](https://www.pasternack.com/hermetic-seal-solder-contact-0.018-pin-diameter-0.109-body-0.18-pin-pe1017-7-p.aspx)

URL: <https://www.pasternack.com/hermetic-seal-solder-contact-0.018-pin-diameter-0.109-body-0.18-pin-pe1017-7-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE1017-7 CAD Drawing

Hermetic Seal Solder Contact with 0.018" Diameter Full Radius Pin, 0.110" Body Diameter and 0.312" Pin Length

