

Hermetically Sealed 2.92mm Female to 2.92mm Female Bulkhead Mount Adapter, 40GHz VSWR1.25, MIL-STD-348B, Bulkhead Thermo Vacuum 1x10-6 TORR



**PE1343**

**Configuration**

- 2.92mm Female Connector 1
- 2.92mm Female Connector 2
- 50 Ohms Impedance
- Straight Body Geometry
- Bulkhead Mount Method

**Features**

- Max VSWR of 1.25:1 up to 40 GHz
- Hermetically Sealed
- 2.92mm interface compliant with MIL-STD-348B
- Gold Plated Beryllium Copper Contact

**Applications**

- General Purpose Test
- Vacuum Test Environment
- Rack Mounted Equipment

**Description**

Pasternack's PE1343 hermetically sealed 2.92mm female to 2.92mm female bulkhead adapter is part of our full line of RF components available for same-day shipping. The 2.92mm connector mates mechanically with commercially available SMA and 3.5mm connectors. Our 2.92mm to 2.92mm adapter has a female to female gender configuration built of durable stainless steel. PE1343 2.92mm female to 2.92mm female adapter operates to 40 GHz. The Pasternack RF adapter provides excellent VSWR of 1.25:1 maximum. This RF 2.92mm to 2.92mm bulkhead adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. This hermetic 2.92mm to 2.92mm adapter prevents the leakage of gases, making it suitable for high pressure or vacuum applications or whenever an airtight seal is required.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
Impedance		50		Ohms
VSWR			1.25:1	
Insertion Loss			0.5	dB
Operating Voltage (AC)			250	Vrms
Dielectric Withstanding Voltage (AC)			750	Vrms
Insulation Resistance	5,000			MOhms
RF Leakage			100	dB

**Mechanical Specifications**

**Size**

- Length 0.89 in [22.61 mm]
- Width 0.56 in [14.22 mm]
- Height 0.56 in [14.22 mm]

Hermetically Sealed 2.92mm Female to 2.92mm Female Bulkhead Mount Adapter, 40GHz VSWR1.25, MIL-STD-348B, Bulkhead Thermo Vacuum 1x10<sup>-6</sup> TORR



## PE1343

Weight	0.02 lbs [9.07 g]	
Description	Connector 1	Connector 2
Polarity	Standard	Standard
Interface Specification	MIL-STD-348B	MIL-STD-348B
Connector Option	Hermetically Sealed	Hermetically Sealed
Mating Cycles, Min	500	500
Mating Torque	11.47 in-lbs 1.30 Nm min	11.47 in-lbs 1.30 Nm min
Contact Captivation Axial Force, Min	4.9 lbs [2.22 kg]	4.9 lbs [2.22 kg]
Coupling Proof Torque	15 in-lbs [1.7 Nm]	15 in-lbs [1.7 Nm]

### Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	2.92mm Female		2.92mm Female	
Contact	Beryllium Copper	Gold	Beryllium Copper	Gold
Insulation	PEI		PEI	
Outer Conductor	Stainless Steel	Passivated	Stainless Steel	Passivated
Body	Stainless Steel	Passivated	Stainless Steel	Passivated

### Environmental Specifications

#### Temperature

Operating Range

Humidity

Thermal Shock

Salt Spray

Hermetic Seal

-30 to +165 °C

MIL-STD-202, Method 206

MIL-STD-202, Method 107, Condition B

MIL-STD-202, Method 101, Condition B

1\*10<sup>-8</sup> cc/sec of HELIUM at 1 ATM

Hermetically Sealed 2.92mm Female to 2.92mm Female Bulkhead Mount Adapter, 40GHz VSWR1.25, MIL-STD-348B, Bulkhead Thermo Vacuum 1x10<sup>-6</sup> TORR



## PE1343

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Hermetically Sealed 2.92mm Female to 2.92mm Female Bulkhead Mount Adapter, 40GHz VSWR1.25, MIL-STD-348B, Bulkhead Thermo Vacuum 1x10<sup>-6</sup> TORR from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Hermetically Sealed 2.92mm Female to 2.92mm Female Bulkhead Mount Adapter, 40GHz VSWR1.25, MIL-STD-348B, Bulkhead Thermo Vacuum 1x10<sup>-6</sup> TORR PE1343](#)

URL: <https://www.pasternack.com/hermetically-sealed-2.92mm-female-to-2.92mm-female-bulkhead-mount-adapter-40ghz-vswr1.25-mil-std-348b-pe1343.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE1343 CAD Drawing

Hermetically Sealed 2.92mm Female to 2.92mm Female Bulkhead Mount Adapter, 40GHz VSWR1.25, MIL-STD-348B, Bulkhead Thermo Vacuum 1x10-6 TORR

