



Violet FAKRA Plug to FAKRA Jack Right Angle  
Cable 48 Inch Length Using RG174 Coax

## RF Cable Assemblies Technical Data Sheet

**PE38753H-48**

### Configuration

- Connector 1: FAKRA Plug
- Connector 2: FAKRA Jack Right Angle
- Cable Type: RG174

### Electrical Specifications

| Description             | Minimum | Typical       | Maximum | Units        |
|-------------------------|---------|---------------|---------|--------------|
| Frequency Range         | DC      |               | 4       | GHz          |
| VSWR                    |         |               | 1.5:1   |              |
| Velocity of Propagation |         | 66            |         | %            |
| Capacitance             |         | 30.8 [101.05] |         | pF/ft [pF/m] |
| Operating Voltage (AC)  |         |               | 335     | Vrms         |

### Mechanical Specifications

#### Cable Assembly

|          |                     |
|----------|---------------------|
| Length*  | 48 in [121.92 cm]   |
| Diameter | 0.37 in [9.4 mm]    |
| Weight   | 0.048 lbs [21.77 g] |

#### Cable

|                                      |                     |
|--------------------------------------|---------------------|
| Cable Type                           | RG174               |
| Impedance                            | 50 Ohms             |
| Inner Conductor Type                 | Stranded            |
| Inner Conductor Material and Plating | Copper Clad Steel   |
| Dielectric Type                      | PE (LD)             |
| Number of Shields                    | 1                   |
| Shield Layer 1                       | Tinned Copper Braid |
| Jacket Material                      | PVC, Black          |
| Jacket Diameter                      | 0.1 in [2.54 mm]    |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Violet FAKRA Plug to FAKRA Jack Right Angle Cable 48 Inch Length Using RG174 Coax PE38753H-48](#)



Violet FAKRA Plug to FAKRA Jack Right Angle  
Cable 48 Inch Length Using RG174 Coax

## RF Cable Assemblies Technical Data Sheet

**PE38753H-48**

### Connectors

| Description                          | Connector 1           | Connector 2            |
|--------------------------------------|-----------------------|------------------------|
| Type                                 | FAKRA Plug            | FAKRA Jack Right Angle |
| Impedance                            | 50 Ohms               | 50 Ohms                |
| Configuration                        | Straight              | Right Angle            |
| Contact Material and Plating         | Phosphor Bronze, Gold | Phosphor Bronze, Gold  |
| Dielectric Type                      | Teflon                | Teflon/Delrin          |
| Outer Conductor Material and Plating | Brass, Nickel         | Brass, Nickel          |
| Body Material and Plating            | Plastic               | Plastic                |

Mechanical Specification Notes:

\*All cable assemblies have a length tolerance of 1.5% or  $\pm 3/8"$ , whichever is greater.

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Violet FAKRA Plug to FAKRA Jack Right Angle Cable 48 Inch Length Using RG174 Coax PE38753H-48](#)



Violet FAKRA Plug to FAKRA Jack Right Angle  
Cable 48 Inch Length Using RG174 Coax

## RF Cable Assemblies Technical Data Sheet

**PE38753H-48**

### How to Order

Part Number Configuration:

**PE38753H**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE38753H-12 = 12 inches long cable  
PE38753H-100cm = 100 cm long cable

Violet FAKRA Plug to FAKRA Jack Right Angle Cable 48 Inch Length Using RG174 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Violet FAKRA Plug to FAKRA Jack Right Angle Cable 48 Inch Length Using RG174 Coax PE38753H-48](https://www.pasternack.com/fakra-plug-fakra-jack-rg174au-cable-assembly-pe38753h-48-p.aspx)

URL: <https://www.pasternack.com/fakra-plug-fakra-jack-rg174au-cable-assembly-pe38753h-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE38753H-48 CAD Drawing

Violet FAKRA Plug to FAKRA Jack Right Angle Cable 48 Inch Length Using RG174 Coax



| How To Order                                                                                                                                                                                                                                            |                                                                                                                     |                                                                                   |               |                  |             |                       |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|---------------|------------------|-------------|-----------------------|
| <div>Part Number Configuration</div> <div>PE3 <div>zzz</div> <div>yy</div> - <div>xx</div> <div>uu</div></div> <div>00 - 99999</div> <div>LF = RoHS Compliant</div> <div>&lt; Blank &gt; = Standard</div> <div>Note: LF applies only to RF cables</div> | <div>Examples</div> <div>PE3000LF-100</div> <div>PE3000-100</div> <div>PE3000LF-100CM</div> <div>PE3000-100CM</div> | <div>CM = Centimeters</div> <div>&lt; Blank &gt; = Inches</div> <div>Length</div> | Part # Ext.   | Length In Inches | Part # Ext. | Length In Centimeters |
|                                                                                                                                                                                                                                                         |                                                                                                                     |                                                                                   | -12           | 12"              | -25CM       | 25Cm                  |
|                                                                                                                                                                                                                                                         |                                                                                                                     |                                                                                   | -24           | 24"              | -50CM       | 50Cm                  |
|                                                                                                                                                                                                                                                         |                                                                                                                     |                                                                                   | -36           | 36"              | -75CM       | 75Cm                  |
|                                                                                                                                                                                                                                                         |                                                                                                                     |                                                                                   | -48           | 48"              | -100CM      | 100Cm                 |
|                                                                                                                                                                                                                                                         |                                                                                                                     |                                                                                   | -60           | 60"              | -125CM      | 125Cm                 |
|                                                                                                                                                                                                                                                         |                                                                                                                     |                                                                                   | Custom Length |                  |             | -xx                   |

- NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
  3. DIMENSIONS ARE IN INCHES [mm].
  4. LENGTH TOLERANCE IS  $\pm 1.5\%$  OR  $3/8"$ , WHICHEVER IS GREATER.

DWG TITLE

**PE38753H**

**PASTERNAK®**  
 Pasternack Enterprises, Inc.  
 P.O. Box 16759 | Irvine | CA | 92623  
**Phone:** (949) 261-1920 | **Fax:** (949) 261-7451  
**Website:** www.pasternack.com | **E-Mail:** sales@pasternack.com

**FSCM NO. 53919**

CAD FILE 41613

SCALE N/A

SIZE A