



Violet FAKRA Plug to FAKRA Jack Right Angle
Cable 36 Inch Length Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE38757H-36

Configuration

- Connector 1: FAKRA Plug
- Connector 2: FAKRA Jack Right Angle
- Cable Type: RG316

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.5:1	
Velocity of Propagation		66		%
Capacitance		32 [104.99]		pF/ft [pF/m]
Operating Voltage (AC)			335	Vrms

Mechanical Specifications

Cable Assembly

Length*	36 in [914.4 mm]
Diameter	0.37 in [9.4 mm]
Weight	0.049 lbs [22.23 g]

Cable

Cable Type	RG316
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.098 in [2.49 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Violet FAKRA Plug to FAKRA Jack Right Angle Cable 36 Inch Length Using RG316 Coax PE38757H-36](#)



Violet FAKRA Plug to FAKRA Jack Right Angle
Cable 36 Inch Length Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE38757H-36

Connectors

Description	Connector 1	Connector 2
Type	FAKRA Plug	FAKRA Jack Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Dielectric Type	Teflon	Teflon/Delrin
Outer Conductor Material and Plating	Brass, Nickel	Brass, Nickel
Body Material and Plating	Plastic	Plastic

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8"$, whichever is greater.

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Violet FAKRA Plug to FAKRA Jack Right Angle Cable 36 Inch Length Using RG316 Coax PE38757H-36](#)



Violet FAKRA Plug to FAKRA Jack Right Angle
Cable 36 Inch Length Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE38757H-36

How to Order

Part Number Configuration:

PE38757H

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE38757H-12 = 12 inches long cable
PE38757H-100cm = 100 cm long cable

Violet FAKRA Plug to FAKRA Jack Right Angle Cable 36 Inch Length Using RG316 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Violet FAKRA Plug to FAKRA Jack Right Angle Cable 36 Inch Length Using RG316 Coax PE38757H-36](https://www.pasternack.com/fakra-plug-fakra-jack-rg316u-cable-assembly-pe38757h-36-p.aspx)

URL: <https://www.pasternack.com/fakra-plug-fakra-jack-rg316u-cable-assembly-pe38757h-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE38757H-36 CAD Drawing

Violet FAKRA Plug to FAKRA Jack Right Angle Cable 36 Inch Length Using RG316 Coax



How To Order						
Part Number Configuration			Examples			
PE3 zzz yy - xx uu			PE3000LF-100		-12	12"
			PE3000-100		-24	24"
00 - 99999			PE3000LF-100CM		-36	36"
< Blank > = Standard			PE3000-100CM		-48	48"
Note: LF applies only to RF cables			PE3000-100CM		-60	60"
					-xx	Custom Length
					-xxCM	Custom Length

- NOTES:
- 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 - 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 - 3. DIMENSIONS ARE IN INCHES [mm].
 - 4. LENGTH TOLERANCE IS $\pm 1.5\%$ OR $3/8"$, WHICHEVER IS GREATER.

DWG TITLE
PE38757H

PE PASTERNAK®
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | **Fax:** (949) 261-7451
Website: www.pasternack.com | **E-Mail:** sales@pasternack.com

FSCM NO. 53919

CAD FILE 41613
SCALE N/A
SIZE A