



Snap-On MMBX Plug Right Angle to Reverse Polarity SMA Female Bulkhead Cable 4 Inch Length Using RG316-DS Coax

RF Cable Assemblies Technical Data Sheet


PE3C4055-4

Configuration

- Connector 1: Snap-On MMBX Plug Right Angle
- Connector 2: SMA Female Reverse Polarity Bulkhead
- Cable Type: RG316-DS

Features

- Max. Operating Frequency of 3 GHz
- Snap-On mating
- Low Profile Right Angle Configurations
- SMA Bulkhead, N Bulkhead and TNC Bulkhead Between-Series Configurations



Applications

- General Purpose Test
- PCB Testing
- PCB Probing
- PCB-to-Panel

Description

Pasternack's MMBX cable assemblies are part of our full line of RF components available for same-day shipping. These MMBX cable assemblies are designed to connect MMBX system components or test connections, delivering signal frequencies as high as 3 GHz. Our family of MMBX cables can also be used to connect from PCB to panel, offering between series MMBX options with SMA Bulkhead, TNC Bulkhead and N Bulkhead assembly configurations. If none of our standard options fit your application, you can specify your own custom MMBX cable assembly using Pasternack's online Cable Creator.

Our MMBX cable assembly datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave cable assemblies allow designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right cable assemblies for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------|---------|--------------|---------|--------------|
| Frequency Range | DC | | 3 | GHz |
| VSWR | | | 1.4:1 | |
| Return Loss | | -15.56 | | dB |
| Insertion Loss | | | 0.36 | dB |
| Velocity of Propagation | | 70 | | % |
| Capacitance | | 29.4 [96.46] | | pF/ft [pF/m] |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Snap-On MMBX Plug Right Angle to Reverse Polarity SMA Female Bulkhead Cable 4 Inch Length Using RG316-DS Coax PE3C4055-4](#)



Snap-On MMBX Plug Right Angle to Reverse Polarity SMA
Female Bulkhead Cable 4 Inch Length Using RG316-DS Coax

RF Cable Assemblies Technical Data Sheet

PE3C4055-4

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency | 0.1 | 0.25 | 0.5 | 1 | 3 | GHz |
| Insertion Loss (Max.) | 0.23 | 0.25 | 0.27 | 0.29 | 0.36 | dB |

Mechanical Specifications

Cable Assembly

| | |
|----------|--------------------|
| Length* | 4 in [101.6 mm] |
| Diameter | 0.312 in [7.92 mm] |

Cable

| | |
|--------------------------------------|----------------------------|
| Cable Type | RG316-DS |
| Impedance | 50 Ohms |
| Inner Conductor Type | Stranded |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type | PTFE |
| Number of Shields | 2 |
| Shield Layer 1 | Silver Plated Copper Braid |
| Shield Layer 2 | Silver Plated Copper Braid |
| Jacket Material | FEP, Tan |
| Jacket Diameter | 0.114 in [2.9 mm] |
| Repeated Minimum Bend Radius | 0.6 in [15.24 mm] |

Connectors

| Description | Connector 1 | Connector 2 |
|--------------------------------------|------------------------|--------------------------------------|
| Type | MMBX Plug Right Angle | SMA Female Reverse Polarity Bulkhead |
| Impedance | 50 Ohms | 50 Ohms |
| Connection Method | Snap-On | |
| Mating Cycles | 100 | |
| Contact Material and Plating | Beryllium Copper, Gold | Gold |
| Dielectric Type | PTFE | PTFE |
| Outer Conductor Material and Plating | Brass, Gold | |
| Body Material and Plating | Brass, Gold | Brass, Nickel |

Mechanical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Snap-On MMBX Plug Right Angle to Reverse Polarity SMA Female Bulkhead Cable 4 Inch Length Using RG316-DS Coax PE3C4055-4](#)



Snap-On MMBX Plug Right Angle to Reverse Polarity SMA Female Bulkhead Cable 4 Inch Length Using RG316-DS Coax

RF Cable Assemblies Technical Data Sheet

PE3C4055-4

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8$ ", whichever is greater.

Environmental Specifications

Temperature

Operating Range -55 to +155 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

PE3C4055 - xx uu

Unit of Measure:
 cm = Centimeters
 <blank> = Inches
 Length
 Base Number

Example: PE3C4055-12 = 12 inches long cable
 PE3C4055-100cm = 100 cm long cable

Snap-On MMBX Plug Right Angle to Reverse Polarity SMA Female Bulkhead Cable 4 Inch Length Using RG316-DS Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Snap-On MMBX Plug Right Angle to Reverse Polarity SMA Female Bulkhead Cable 4 Inch Length Using RG316-DS Coax PE3C4055-4](#)

URL: <https://www.pasternack.com/mmbx-plug-sma-female-rg316-ds-cable-assembly-pe3c4055-4-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C4055-4 CAD Drawing

Snap-On MMBX Plug Right Angle to Reverse Polarity SMA Female Bulkhead Cable 4 Inch Length Using RG316-DS Coax



| STANDARD TOLERANCES | |
|---------------------|--------|
| .X | ±0.2 |
| .XX | ±0.01 |
| .XXX | ±0.005 |

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES



Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | **Fax:** (949) 261-7451
Website: www.pasternack.com | **E-Mail:** sales@pasternack.com

DWG TITLE

PE3C4055

NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME
 3. DIMENSIONS ARE IN INCHES [mm].

CAGE CODE 53919

CAD FILE 052317

SCALE N/A

SIZE A

9999