



7/16 DIN Male to N Female Cable Using RG8 Coax

RF Cable Assemblies Technical Data Sheet

PE3W07200

Configuration

- Connector 1: 7/16 DIN Male
- Connector 2: N Female
- Cable Type: RG8

Features

- 66% Phase Velocity
- PVC (NC) Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W07200 7/16 DIN male to type N female cable using RG8 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack 7/16 DIN to type N cable assembly has a male to female gender configuration with 50 ohm flexible RG8 coax.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Weight 0.427 lbs [193.68 g]

Cable

Cable Type RG8
Impedance 50 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper
Dielectric Type PE
Number of Shields 1
Shield Layer 1 Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [7/16 DIN Male to N Female Cable Using RG8 Coax PE3W07200](#)



7/16 DIN Male to N Female Cable Using RG8 Coax

RF Cable Assemblies Technical Data Sheet

PE3W07200

Jacket Material
Jacket Diameter

PVC (NC), Black
0.405 in [10.29 mm]

Connectors

Description	Connector 1	Connector 2
Type	7/16 DIN Male	N Female
Impedance	50 Ohms	50 Ohms
Body Material and Plating	Brass, Nickel	Brass, Nickel

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [7/16 DIN Male to N Female Cable Using RG8 Coax PE3W07200](#)



7/16 DIN Male to N Female Cable Using RG8 Coax

RF Cable Assemblies Technical Data Sheet

PE3W07200

How to Order

Part Number Configuration:

PE3W07200

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W07200-12 = 12 inches long cable
PE3W07200-100cm = 100 cm long cable

7/16 DIN Male to N Female Cable Using RG8 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [7/16 DIN Male to N Female Cable Using RG8 Coax PE3W07200](https://www.pasternack.com/7-16-din-male-to-n-female-cable-using-rg8-pe3w07200-p.aspx)

URL: <https://www.pasternack.com/7-16-din-male-to-n-female-cable-using-rg8-pe3w07200-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W07200 CAD Drawing

7/16 DIN Male to N Female Cable Using RG8 Coax

