



## SMP Female to SMP Female Adapter, Up to 8 GHz, .562 inch Special Length

### RF Adapters Technical Data Sheet

PE91099

#### Configuration

- SMP Female Connector 1
- SMP Female Connector 2
- 50 Ohm
- Straight Body Geometry

#### Features

- Gold Plated Beryllium Copper Contact

#### Applications

- General Purpose Test

#### Description

Pasternack's PE91099 SMP female to SMP female adapter is part of our full line of RF components available for same-day shipping. Our SMP to SMP adapter has a female to female gender configuration. PE91099 SMP female to SMP female adapter is gold plated and operates to 40 GHz.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
Operating Voltage (AC)			335	Vrms
Dielectric Withstanding Voltage (AC)			500	Vrms
Inner Conductor DC Resistance			6	mOhms
Outer Conductor DC Resistance			2	mOhms
Insulation Resistance	5,000			MOhms

#### Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 8	8 to 26.5				GHz
VSWR, Max	1.1:1	1.35:1				

Electrical Specification Notes:  
Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female to SMP Female Adapter, Up to 8 GHz, .562 inch Special Length PE91099](#)



# SMP Female to SMP Female Adapter, Up to 8 GHz, .562 inch Special Length

## RF Adapters Technical Data Sheet

PE91099

### Mechanical Specifications

#### Size

Length	0.562 in [14.27 mm]
Width	0.135 in [3.43 mm]
Weight	0.0023 lbs [1.04 g]

Description	Connector 1	Connector 2
Type	SMP Female	SMP Female
Polarity	Standard	Standard

#### Mechanical Specification Notes:

SMP mating cycles: 1,000 (smooth bore), 500 (limited detent), 100 (full detent) minimum.

### Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	SMP Female		SMP Female	
Contact	Beryllium Copper	Gold	Beryllium Copper	Gold
Insulation	PTFE		PTFE	
Outer Conductor	Beryllium Copper	Gold	Beryllium Copper	Gold
Body	Brass	Gold	Brass	Gold

### Environmental Specifications

#### Temperature

Operating Range	-40 to +125 deg C
-----------------	-------------------

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female to SMP Female Adapter, Up to 8 GHz, .562 inch Special Length PE91099](#)



## SMP Female to SMP Female Adapter, Up to 8 GHz, .562 inch Special Length

### RF Adapters Technical Data Sheet

PE91099

SMP Female to SMP Female Adapter, Up to 8 GHz, .562 inch Special Length from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female to SMP Female Adapter, Up to 8 GHz, .562 inch Special Length PE91099](https://www.pasternack.com/smp-female-smp-female-straight-adapter-pe91099-p.aspx)

URL: <https://www.pasternack.com/smp-female-smp-female-straight-adapter-pe91099-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE91099 CAD Drawing

SMP Female to SMP Female Adapter, Up to 8 GHz, .562 inch Special Length



NOTES:  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE  
**PE91099**

FSCM NO. 53919

CAD FILE 011116

SCALE N/A

SIZE A

150



Pasternack Enterprises, Inc.  
 P.O. Box 16759 | Irvine | CA | 92623  
 Phone: (949) 261-1920 | Fax: (949) 261-7451  
 Website: www.pasternack.com | E-Mail: sales@pasternack.com