



Fixed Antenna Operates From 2.4 GHz to 2.5 GHz With a Maximum 11 dBi Gain N Female Input Connector

TECHNICAL DATA SHEET

PE51141

Configuration

Design Frequency Range Polarization Interface 1 Number of Output Ports Fixed 2.4 to 2.5 GHz Vertical N Female

Electrical Specifications (Values at 25°C, sea level)

Description	Minimum	Typical	Maximum	Units
Impedance		50		Ohms
Gain Variation		1		dBi
Input Power			150	Watts
Input VSWR			1.5:1	

Mechanical Specifications

Radome Material **Temperature**

Operating Range

Fiberglass

-40 to +60 deg C

Size

Length Weight Wind Loading Humidity

3.6 in [91.44 mm] 6.6 lbs [2.99 Kg] 150 MPH [241.4 KPH] 5% - 95 %

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant

Plotted and Other Data

- Values at 25 °C, sea level
- · Lightning Protection added by direct grounding.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Fixed Antenna Operates From 2.4 GHz to 2.5 GHz With a Maximum 11 dBi Gain N Female Input Connector PE51141

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com






Fixed Antenna Operates From 2.4 GHz to 2.5 GHz With a Maximum 11 dBi Gain N Female Input Connector

TECHNICAL DATA SHEET

PE51141

Outline Drawing



Fixed Antenna Operates From 2.4 GHz to 2.5 GHz With a Maximum 11 dBi Gain N Female Input Connector from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Fixed Antenna Operates From 2.4 GHz to 2.5 GHz With a Maximum 11 dBi Gain N Female Input Connector PE51141

URL: http://www.pasternack.com/fixed-antenna-2.4-2.5-ghz-11-dbi-gain-n-female-pe51141-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com