



SMP Male Limited Detent Shroud 2 Hole
Flange Mount 0.481 Inch Hole Spacing

TECHNICAL DATA SHEET

PE44949

Configuration

Connector	SMP Male, Limited Detent
Connector Specification	DESC 94007
Connector Interface Type	None
Attachment Method (Shield/Contact)	None
Body Style	Straight
Mount Method	2 Hole Flange

Electrical Specifications

Impedance	50 Ohms
-----------	---------

Mechanical Specifications

Size

Length	0.625 in [15.88 mm]
Width/Dia.	0.223 in [5.66 mm]
Height	0.12 in [3.05 mm]
Weight	0.082 lbs [37.19 g]

Connector

Type	SMP Male
Body Material and Plating	Passivated Stainless Steel
Body Plating Specification	QQ-P-35

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Male Limited Detent Shroud 2 Hole Flange Mount 0.481 Inch Hole Spacing PE44949](#)



SMP Male Limited Detent Shroud 2 Hole
Flange Mount 0.481 Inch Hole Spacing

TECHNICAL DATA SHEET

PE44949

Plotted and Other Data

Notes:

- Values at +25 °C, sea level

SMP Male Limited Detent Shroud 2 Hole Flange Mount 0.481 Inch Hole Spacing from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Male Limited Detent Shroud 2 Hole Flange Mount 0.481 Inch Hole Spacing PE44949](#)

URL: <http://www.pasternack.com/smp-male-standard-shroud-pe44949-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE44949 CAD Drawing

SMP Male Limited Detent Shroud 2 Hole Flange Mount 0.481 Inch Hole Spacing



NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
PE44949
 FSCM NO. 53919
 CAD FILE 110413
 SCALE N/A
 SIZE A
 150

PE PASTERNAK®
 Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
 Phone: (949) 261-1920 | Fax: (949) 261-7451
 Website: www.pasternack.com | E-Mail: sales@pasternack.com