

WR-42 Square Cover Flange to End Launch 2.92mm Female Waveguide to Coax Adapter Operating From 18 GHz to 26.5 GHz, K Band



Waveguide to Coax Adapters Technical Data Sheet

PE9878

Features

- K Band, 18 to 26.5 GHz Frequency Range
- WR-42 Waveguide Interface with Square Cover Flange
- 2.92mm Female Coaxial Interface

 Comprehensive waveguide offerings also include E-Bends, H-Bends, Sections, Filters, Terminations, Couplers, and more.

Description

The PE9878 is a waveguide to coaxial adapter operating in the K band with a 18 to 26.5 GHz frequency range. This adapter offers a WR-42 waveguide interface size coupled with a precision tolerance square cover flange. The PE9878 is constructed of aluminum to ensure durability and repeatable RF performance. The coaxial connector offered by this adapter uses a 2.92mm geometry endorsed by International Electrotechnical Commission (IEC). The 2.92mm female connector mates with commercially available SMA and 3.5mm connectors. The package is REACH and RoHS compliant.

Configuration

Waveguide Size Flange RF Connector Impedance Body Geometry WR-42 Square Cover 2.92mm Female 50 Ohms End Launch

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	18		26.5	GHz
VSWR			1.4:1	
Input Power (Peak)			25	Watts

Mechanical Specifications

Size

 Length
 0.87 in [22.1 mm]

 Width
 0.87 in [22.1 mm]

 Height
 1.39 in [35.31 mm]

 Weight
 0.2 lbs [90.72 g]

RF Connector

Connector Type 2.92mm Female Body Material and Plating Stainless Steel

Waveguide Interface

Waveguide Type WR-42 Flange Type Square Cover

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-42 Square Cover Flange to End Launch 2.92mm Female Waveguide to Coax Adapter Operating From 18 GHz to 26.5 GHz, K Band PE9878

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



WR-42 Square Cover Flange to End Launch 2.92mm Female Waveguide to Coax Adapter Operating From 18 GHz to 26.5 GHz, K Band



Waveguide to Coax Adapters Technical Data Sheet

PE9878

Body Material and Plating

Aluminum

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant


REACH Compliant 12/17/2015

Plotted and Other Data

Notes:

Values at +25 °C, sea level unless stated otherwise

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-42 Square Cover Flange to End Launch 2.92mm Female Waveguide to Coax Adapter Operating From 18 GHz to 26.5 GHz, K Band PE9878

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451



WR-42 Square Cover Flange to End Launch 2.92mm Female Waveguide to Coax Adapter Operating From 18 GHz to 26.5 GHz, K Band



Waveguide to Coax Adapters Technical Data Sheet

PE9878

WR-42 Square Cover Flange to End Launch 2.92mm Female Waveguide to Coax Adapter Operating From 18 GHz to 26.5 GHz, K Band from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-42 Square Cover Flange to End Launch 2.92mm Female Waveguide to Coax Adapter Operating From 18 GHz to 26.5 GHz, K Band PE9878

URL: http://www.pasternack.com/wr-42-2.92mm-female-waveguide-coax-adapter-18-26.5-ghz-pe9878-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE9878 CAD Drawing

WR-42 Square Cover Flange to End Launch 2.92mm Female Waveguide to Coax Adapter Operating From 18 GHz to 26.5 GHz, K Band

