

BMA Plug Right Angle Connector Solder Attachment Thru Hole PCB



RF Connectors Technical Data Sheet

Configuration

- BMA Plug Connector
- 50 Ohms
- Right Angle Body Geometry

Features

- Max. Operating Frequency 22 GHz
- Excellent VSWR of 1.25:1
- Gold Plated Brass Contact

Applications

- General Purpose Test
- PCB Applications

Description

Pasternack's PE45355 BMA plug right angle connector with solder attachment for thru hole PCB is part of our full line of RF components available for same-day shipping. Our BMA plug connector operates up to a maximum frequency of 22 GHz and offers excellent VSWR of 1.25:1. The Pasternack blind mate connector is ideal for applications where direct visual or tactile access to the connection point is not possible, for example, when two circuit boards need to be mated. Its right angle body geometry allows for easier connections in tight spaces.

• Thru Hole Interface Type

• 31.49µ in. minimum contact plating

Solder Attachment

Blind Mate Connector

Our BMA plug right angle connector PE45355 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		22	GHz
VSWR			1.25:1	
Insertion Loss			3.75	dB
Operating Voltage (AC)			350	Vrms
Dielectric Withstanding Voltage (AC)			1,000	Vrms
Insulation Resistance	5,000			MOhms

Mechanical Specifications

Size	
Length	0.6 in [15.24 mm]
Width/Dia.	0.25 in [6.35 mm]
Height	0.68 in [17.27 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: BMA Plug Right Angle Connector Solder Attachment Thru Hole PCB PE45355

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE45355



BMA Plug Right Angle Connector Solder Attachment Thru Hole PCB



PE45355

RF Connectors Technical Data Sheet

V	Veight	0.011	bs [4.99 g]		
Ν	Nating Cycles	500 C	500 Cycles		
Ν	laterial Specifications				
	Description	Material	Plating		
C	Contact	Brass	Gold 31.49µ in. minimum		
Ir	nsulation	PTFE			
E	Body	Stainless Steel	Gold 19.68µ in. minimum		
	ronmental Specifications				
	Operating Range	-65 to	-65 to +125 deg C		
Compliance Certifications (see product page for current document)					
	red and Other Data Notes:				
BMA Plug Right Angle Connector Solder Attachment Thru Hole PCB from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.					
Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: BMA Plug Right Angle Connector Solder Attachment Thru Hole PCB PE45355					
URL: https://www.pasternack.com/bma-plug-thru-hole-pcb-connector-pe45355-p.aspx					
The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.					

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE45355 CAD Drawing

BMA Plug Right Angle Connector Solder Attachment Thru Hole PCB

