

75 Ohm N Male Connector Crimp/Non-Solder Contact Attachment for LMR-600-75, LMR-600-75-DB, LMR-600-75-FR

EZ-600-NMH-75

Configuration

- N Male Connector
- 75 Ohms
- Straight Body Geometry
- Connector Interface Types: LMR-600-75, LMR-600-75-DB, LMR-600-75-FR

Features

- Max. Operating Frequency 2 GHz
- Gold Plated Beryllium Copper Contact

Applications

- General Purpose Test
- Custom Cable Assemblies

Description

Times Microwave's EZ-600-NMH-75 type N , N , Connector is part of our full line of RF components available for same-day shipping. Times Microwave's type N male connector operates up to a maximum frequency of 2 GHz.

Times Microwave's 75 ohm type N male connector EZ-600-NMH-75 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		2	GHz
Dielectric Withstanding Voltage (AC)			2,500	Vrms
Impedance		75		Ohms

Mechanical Specifications

Size

Length	0.87 in [22.1 mm]
Width	0.87 in [22.1 mm]
Height	2.1 in [53.34 mm]
Weight	0.166 lbs [75.3 g]

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold
Insulation	PTFE	
Body	Nickel	Gold
Gasket	Silicone	
Crimp Sleeve	Copper	Gold
Shrink Tubing	Polyolefin	

75 Ohm N Male Connector Crimp/Non-Solder Contact Attachment for LMR-600-75, LMR-600-75-DB, LMR-600-75-FR

EZ-600-NMH-75

Environmental Specifications

Temperature

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

75 Ohm N Male Connector Crimp/Non-Solder Contact Attachment for LMR-600-75, LMR-600-75-DB, LMR-600-75-FR from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm N Male Connector Crimp/Non-Solder Contact Attachment for LMR-600-75, LMR-600-75-DB, LMR-600-75-FR EZ-600-NMH-75](#)

URL: <https://www.pasternack.com/n-male-lmr-600-75-connector-ez-600-nmh-75-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

75 Ohm N Male Connector Crimp/Non-Solder Contact Attachment
for LMR-600-75, LMR-600-75-DB, LMR-600-75-FR

