



Directional 20 dB SMA Coupler From 1 GHz to 18 GHz Rated To 25 Watts

TECHNICAL DATA SHEET

PE2214-20

Directional 20 dB SMA Coupler From 1 GHz to 18 GHz Rated To 25 Watts

_	-			
Co	nfid	aur	ati	on

Connector 1 SMA Female
Connector 2 SMA Female
Connector 3 SMA Female
Design Directional Coupler

Electrical Specifications

Frequency Range, GHz 1 to 18 Directivity, dB 15 Impedance, Ohms 50 Maximum Insertion Loss, dB 8.0 Maximum Input Power, Watts 25 Maximum Input VSWR 1.5:1 Maximum Operating Voltage, Vrms 25 Coupling Value, dB 20 Coupling Tolerance, dB

Mechanical Specifications

Size

 Length, in [mm]
 4.26 [108.2]

 Width, in [mm]
 0.4 [10.16]

 Height, in [mm]
 1.2 [30.48]

Connector 1

Type SMA Female

Connector 2

Type SMA Female

Connector 3

Type SMA Female

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Directional 20 dB SMA Coupler From 1 GHz to 18 GHz Rated To 25 Watts PE2214-20

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.





Directional 20 dB SMA Coupler From 1 GHz to 18 GHz Rated To 25 Watts

TECHNICAL DATA SHEET

PE2214-20

Compliance Certifications (visit www.Pasternack.com for current document)

Plotted and Other Data

Notes:

Values at 25 °C, sea level

Directional 20 dB SMA Coupler From 1 GHz to 18 GHz Rated To 25 Watts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Directional 20 dB SMA Coupler From 1 GHz to 18 GHz Rated To 25 Watts PE2214-20

URL: http://www.pasternack.com/directional-20-db-sma-coupler-1-18-ghz-25-watts-pe2214-20-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

PE2214-20 CAD Drawing
Directional 20 dB SMA Coupler From 1 GHz to 18 GHz Rated To 25 Watts

