



RP MCX Jack Connector Solder Attachment Thru Hole PCB, .200 inch x .067 inch Hole Spacing

TECHNICAL DATA SHEET

PE44375

RP MCX Jack Connector Solder Attachment Thru Hole PCB, .200 inch x .067 inch Hole Spacing

Configuration

| | |
|--|---------------------------|
| Connector | MCX Jack Reverse Polarity |
| Connector Interface Type | Thru Hole |
| Cable Attachment Method (Shield/Contact) | Solder |
| Body Style | Straight |

Electrical Specifications

| | |
|-----------------|----|
| Impedance, Ohms | 50 |
|-----------------|----|

Mechanical Specifications

Size

| | |
|---------------------|--------------|
| Length, in [mm] | 0.425 [10.8] |
| Width/Dia., in [mm] | 0.236 [5.99] |
| Height, in [mm] | 0.236 [5.99] |
| Weight, lbs [g] | 0.004 [1.81] |

Connector

| | |
|------------------------------|---------------------------|
| Type | MCX Jack Reverse Polarity |
| Contact Material and Plating | Gold |
| Body Material and Plating | Brass, Gold |
| Dielectric Type | PTFE |

Compliance Certifications (visit www.Pasternack.com for current document)

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Plotted and Other Data

| | |
|--------|----------------------------|
| Notes: | Values at 25 °C, sea level |
|--------|----------------------------|

RP MCX Jack Connector Solder Attachment Thru Hole PCB, .200 inch x .067 inch Hole Spacing from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [RP MCX Jack Connector Solder Attachment Thru Hole PCB, .200 inch x .067 inch Hole Spacing PE44375](http://www.pasternack.com/mcx-jack-reverse-polarity-thru-hole-pcb-connector-pe44375-p.aspx)

URL: <http://www.pasternack.com/mcx-jack-reverse-polarity-thru-hole-pcb-connector-pe44375-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE44375 CAD Drawing

RP MCX Jack Connector Solder Attachment Thru Hole
PCB, .200 inch x .067 inch Hole Spacing



DWG TITLE

PE44375

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].
4. FITS MIL-C-17 AND EQUIVALENT CABLES.

FSCM NO. 53919

CAD FILE 060203

SCALE N/A

SIZE A

127



Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com