

Commercial Grade N Male to N Female Right Angle Adapter

PE910101



Configuration

- N Male Connector 1
- N Female Connector 2
- 50 Ohms Impedance
- Commercial Grade Design
- Right Angle Body Geometry

Features

- Gold Plated Nickel Contact

Applications

- General Purpose Test

Description

Pasternack's PE910101 type N male to type N female right angle adapter is part of our full line of RF components available for same-day shipping. Our type N to type N adapter has a male to female gender configuration in a commercial grade design. This right angle type N to type N adapter allows for easier connections in tight spaces.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Impedance		50		Ohms

Mechanical Specifications

Size

Length	1.42 in [36.07 mm]
Width	1.35 in [34.29 mm]
Height	0.79 in [20.07 mm]
Weight	0.12 lbs [54.43 g]

Description	Connector 1	Connector 2
Polarity	Standard	Standard

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	N Male		N Female	
Contact	Nickel	Gold	Nickel	Gold

Commercial Grade N Male to N Female Right Angle Adapter

PE910101



Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Insulation	POM		POM	
Outer Conductor	Brass	Nickel	Brass	Nickel
Body	Brass	Nickel	Brass	Nickel
Gasket	Silicone Rubber			
Coupling Nut	Brass	Nickel		

Environmental Specifications

Temperature

Operating Range -55 to +85 °C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Commercial Grade N Male to N Female Right Angle Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Commercial Grade N Male to N Female Right Angle Adapter PE910101](#)

URL: <https://www.pasternack.com/commercial-grade-n-male-to-n-female-right-angle-adapter-pe910101.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE910101 CAD Drawing
Commercial Grade N Male to N Female Right Angle Adapter

